

1		2		3		4		5		6		7		8					
POGO PIN		REAC/ROHS												REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
														A1	NEW	Replace frame			2018.06.12
otes: Characteristics: A. Material (材料) 1) Housing:High Plastic BLACK (UL94V-0) 2) Plunger:brass c6801 3) Barrel:brass c6801 4) Spring:Stainless steel wire. B. Plating (电镀) 1) Plunger:Brass,Plating 3u' Au over Min. 50u' Ni. 2) Barrel:Brass,Plating 3u' Au over Min. 50u' Ni. 3) Spring:Stainless steel wire.Plating Min. 1u' Au C. Electrical (电性能) 1) Operating voltage: 12V Max. 2) Opetating current: 1A Max. 3) Contact resistance: 30mohm Max. at working height(Quiescence). D. Mechanical (机械性能) 1) Total stroke: 1.70mm. 2) Working height: 0.7mm. 3) Spring Force:65gf±10gf at working height 4) Mechanical life: 10,000 cycle min. 5) Don't exceed the Max. allowed compression E. Environmental (环境) 1) Storage and operating temoperature range: -40°C~+85°C 2) Humidity range: 10% RH to 90% RH 3) Salt spray: 48H F. Others (其他) 1) The dimensions marked * are critical, Should be checked in production 2) RoHS compliant product.																			
</																			