



**ES5A-ES5J****Surface Mount Superfast Rectifiers****Features**

- Low profile package
- Ideal for automated placement
- Glass passivated chip junctions
- Fast switching for high efficiency
- High forward surge capability
- High temperature soldering:
260°C/10 seconds at terminals
- Component in accordance to
RoHS 2002/95/1 and WEEE 2002/96/EC

**SMB(DO-214AA)**

Dimensions in inches and (millimeters)

Mechanical Date

- **Case:** JEDEC DO-214AA molded plastic body over glass passivated chip
- **Terminals:** Solder plated, solderable per J-STD-002B and JESD22-B102D
- **Polarity:** Laser band denotes cathode end

Maximum Ratings and Electrical Characteristics Rating at 25 °C

ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	Symbol	ES 5A	ES 5B	ES 5C	ES 5D	ES 5F	ES 5G	ES 5H	ES 5J	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	150	200	300	400	500	600	V
Maximum RMS Voltage	V _{RMS}	35	70	105	140	210	280	350	420	V
Maximum DC Blocking Voltage	V _{DC}	50	100	150	200	300	400	500	600	V
Maximum Average Forward Rectified Current See Fig. 1	I _(AV)	5.0								A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method) @T _J = 100 °C	I _{FSM}	150								A
Maximum Instantaneous Forward Voltage @ 5.0A	V _F	1.0				1.25		1.65		V
Maximum DC Reverse Current @ T _A =25 °C at Rated DC Blocking Voltage @ T _A =100 °C	I _R	10 500								uA uA
Maximum Reverse Recovery Time (Note 1)	T _{rr}	35								nS
Typical Junction Capacitance (Note 2)	C _j	45				30				pF
Typical Thermal Resistance (Note 3)	R _{θJA} R _{θJL}	67 32								°C /W
Operating Temperature Range	T _J	-55 to +150								°C
Storage Temperature Range	T _{STG}	-55 to +150								°C

Notes: 1. Reverse Recovery Test Conditions: $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{RR}=0.25\text{A}$
2. Measured at 1 MHz and Applied $V_R=4.0$ Volts
3. Units Mounted on P.C.B. with 0.6" x 0.6"(16mm x 16mm) Copper Pad Areas



ES5A-ES5J

Surface Mount Superfast Rectifiers

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)









FIG.7- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM

