




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.05.24

- SPECIFICATIONS
- 1.Current rating: 9A AC, DC
 - 2.Voltage rating: 600V AC,DC
 - 3.Temperature range: -25℃ ~ +105℃
 - 4.Insulation resistance: 1000MΩ Min.
 - 5.Withstanding voltage: 1500V AC/ minute.
 - 6.Contact resistance: 10mΩ Max.




Material:
Insulator: Nylon 66 UL 94V-2
Contact: Brass
Plating: Tin plated over Nickel
Circuits: 02~24
Mate with XFCN P4202 series double row male housing

Ordering Code:


M4202R-2xNP	
1	2

- 1.序列号
2.Pin位数:

PART NO.	Dimensions(mm)	
	A	B
2x01	--	5.60
2x02	4.20	9.80
2x03	8.40	14.00
2x04	12.60	18.20
2x05	16.80	22.40
2x06	21.00	26.60
2x07	25.20	30.80
2x08	29.40	35.00
2x09	33.60	39.20
2x10	37.80	43.40
2x11	42.00	47.60
2x12	46.20	51.80



P.C.B LAYOUT



CIRCUIT SIZE LAYOUT

X.±0.50	X.°±	PART NO: M4202R-2xNP	XFCN 兴飞连接器				
.X±0.25	.X°±						
.XX±0.15	.XX°±	TITLE: 4.20mm Crimp Style Connectors	0769-82001899				
.XXX±0.10	.XXX°±		www.xfconn.com				
UNITS:	mm	DWG NO:					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN							
		APPD	Chen ZhiQiang	VIEW			
		CHKD	Liu Wei				
		DRAW	Chen HongJiang	SCALE	SHEET	REV	
DATE	2024.06.28	NONE	1/1	A1			