





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A2		ADDED 2-2337815-7 PN	23AUG2021	VK	GL

26	7000 ⁺¹⁰⁰ ₋₀	4-2337815-8
26	6000 ⁺¹⁰⁰ ₋₀	4-2337815-7
26	5000 ⁺¹⁰⁰ ₋₀	4-2337815-6
26	4000 ⁺⁸⁰ ₋₀	4-2337815-5
26	3000 ⁺⁸⁰ ₋₀	4-2337815-4
26	2000 ⁺⁸⁰ ₋₀	4-2337815-3
26	1000 ⁺⁵⁰ ₋₀	4-2337815-2
26	500 ⁺⁵⁰ ₋₀	4-2337815-1
28	3500 ⁺⁸⁰ ₋₀	2-2337815-7
28	5000 ⁺¹⁰⁰ ₋₀	2-2337815-6
28	4000 ⁺⁸⁰ ₋₀	2-2337815-5
28	3000 ⁺⁸⁰ ₋₀	2-2337815-4
28	2000 ⁺⁸⁰ ₋₀	2-2337815-3
28	1000 ⁺⁵⁰ ₋₀	2-2337815-2
28	500 ⁺⁵⁰ ₋₀	2-2337815-1
30	3000 ⁺⁸⁰ ₋₀	2337815-4
30	2000 ⁺⁸⁰ ₋₀	2337815-3
30	1000 ⁺⁵⁰ ₋₀	2337815-2
30	500 ⁺⁵⁰ ₋₀	2337815-1
AWG	L	PART NO.

1. ASSEMBLY TESTED FOR CONTINUITY, OPENS, SHORTS, EEPROM PROGRAM AND SIGNAL INTEGRITY.
2. ROHS AND REACH COMPLIANCE: PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE SPECIFICATION TEC-138-702.

3 LABEL INFORMATION:



4 LABEL INFORMATION:



5 4-2337815-8 CAN NOT MEET SI SPECIFICATION OF SAS3.0.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KYLIN YAO 05JUN2018	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK KYLIN YAO 05JUN2018	NAME MINI SAS HD TO MINI SAS HD 4X	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± - 4. PLC ± - ANGLES ± -		APVD DAVID ZHANG 05JUN2018	PRODUCT SPEC APPLICATION SPEC	
MATERIAL -		WEIGHT 0	SIZE A1	RESTRICTED TO -
FINISH -		CAGE CODE 00779	DRAWING NO. 2337815	SCALE 1:1
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 2	REV A2

