




额定负荷 Rating	DC 12V/50mA	
接触电阻 Contact Resistance	100mΩ max.	
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.	
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.	
操作力 Operation force	160±30gf	250±50gf
寿命试验 Operating Life	100,000 cycles	
行程 Travels	0.25±0.1mm	




P.C.B MOUNTING PATTERN DIMENSION  
The following soldering patterns are recommended for reflow soldering

### CIRCUIT DIAGRAM



5	端子	黄铜	1	镀镍银
4	弹片	不锈钢	1	覆银
3	基座	PPA黑	1	——
2	盖板	黄铜	1	镀银
1	按钮	PPA红	1	——
项目	名称	材质	数量	表面处理

0~3	± 0.05	± 0.10	± 0.20
>3~6	± 0.05	± 0.10	± 0.30
>6~30	± 0.10	± 0.20	± 0.50
>30~120	± 0.15	± 0.30	± 0.80
未注尺寸公差(mm)			



设计  
Jack Jin  
图面  
单位  
A4  
MM

审核  
Jacky Zhong  
比例  
重量  
1 : 1

批准  
Tony Meng  
页码  
1/1  
版次  
A/0

东莞市美韩电子科技有限公司

Dongguan Usakro Electronic Technology Co., Ltd.

SIZE  
A4  
VER  
R  
DWG NO. 型号 : UK-B0240-R-160JZ  
1 of 1 PART NO. 规格 : 3\*6\*2.5 贴片