





P. C. B LAYOUT

① ② ③
④ ⑤ ⑥

SCHEMATIC

SPECIFICATION

- 1.Rating : DC 12V 0.3A.
- 2.Function: 2P2T
- 3.Contact resistance: $\leq 100m\Omega$.
- 4.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 5.Withstanding voltage: 250VAC .
- 6.Operating Force: $250\pm 100gf$ (依客户需求而定) .
- 7.Life test: 10,000 cycles.
- 8.Sign"* "is importance dimension.

				TOLERANCE UNLESS SPECIFIED										
7	SHELL	PA66	1	BLUE	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0	2024.4.30	初次发行		TQF			
6	TERMINAL	BRASS STRIP	6	Ag PLATED			NO	DATE	REVISIONS		BY	APPD		
5	CASE	PA66	1	BLACK										
4	SPRING	SUS WIRE	1											
3	CONTACT	BRONZE	2	Ag PLATED	MODEL: PB-22E60-N-E-HT				SCALE: 1:1	ROHS COMPLIANT	CHK'D			
2	KNOB	PA66	1	BLUE	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司							APPD		
1	COVER	PPA	1	BLACK										
NO.	PART NAME	MATERIAL	QTY	FINISHING								PRO.AGL:		REV :A0