

IRL2505PBF-VB Datasheet N-Channel 60-V (D-S) MOSFET

PRODUCT	DUCT SUMMARY			
V _{DS} (V)	$R_{DS(on)}(\Omega)$	I _D (A) ^a		
60	0.011 at V _{GS} = 10 V	60		
00	0.013 at V _{GS} = 4.5 V	50		


FEATURES

- 175 °C Junction Temperature
- TrenchFET® Power MOSFET
- Material categorization:









N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS (T _C = 25 °C, unless otherwise noted)					
Parameter		Symbol	Limit	Unit	
Gate-Source Voltage		V _{GS}	± 20	V	
Continuous Dusin Coment /T = 475 °C\h	T _C = 25 °C	1-	60		
Continuous Drain Current (T _J = 175 °C) ^b	T _C = 100 °C	l _D	50 ^a		
Pulsed Drain Current		I _{DM}	200	A	
Continuous Source Current (Diode Conduction)		I _S	50ª		
Avalanche Current		I _{AS}	50		
Single Avalanche Energy (Duty Cycle ≤ 1 %) L = 0.1 mH		E _{AS}	125	mJ	
Mayimum Dayar Dissinction	T _C = 25 °C	Pn	136	W	
Maximum Power Dissipation	T _A = 25 °C		3 ^b , 8.3 ^{b, c}		
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 175	°C	

THERMAL RESISTANCE RATINGS						
Parameter		Symbol	Typical	Maximum	Unit	
Marrian Institut to Amelianda	t ≤ 10 sec	R _{thJA}	15	18		
Maximum Junction-to-Ambient ^a	Steady State		40	50	°C/W	
Maximum Junction-to-Case		R _{thJC}	0.85	1.1		

Notes:

- a. Package limited.
- b. Surface mounted on 1" x 1" FR4 board.
- $c.\ t \leq 10\ s.$

服务热线:400-655-8788



Parameter	Symbol	Test Conditions	Min.	Typ.a	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$	60			V	
Gate Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	1		3	V	
Gate-Body Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 100	nA	
		V _{DS} = 60 V, V _{GS} = 0 V			1		
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 60 V, V _{GS} = 0 V, T _J = 125 °C			50	μΑ	
		V _{DS} = 60 V, V _{GS} = 0 V, T _J = 175 °C			250		
On-State Drain Current ^b	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	60			Α	
		V _{GS} = 10 V, I _D = 20 A		0.011			
	D	V _{GS} = 10 V, I _D = 20 A, T _J = 125 °C		0.014		Ω	
Drain-Source On-State Resistance ^b	R _{DS(on)}	V _{GS} = 10 V, I _D = 20 A, T _J = 175 °C		0.018			
		V _{GS} = 4.5 V, I _D = 15 A		0.013			
Forward Transconductance ^b	9 _{fs}	V _{DS} = 15 V, I _D = 20 A		60		S	
Dynamic							
Input Capacitance	C _{iss}			4200			
Output Capacitance	C _{oss}	$V_{GS} = 0 \text{ V}, V_{DS} = 25 \text{ V}, f = 1 \text{ MHz}$		570		pF	
Reverse Transfer Capacitance	C _{rss}			325			
Total Gate Charge ^c	Qg			47			
Gate-Source Charge ^c	Q_{gs}	$V_{DS} = 30 \text{ V}, V_{GS} = 10 \text{ V}, I_{D} = 50 \text{ A}$		10		nC	
Gate-Drain Charge ^c	Q_{gd}			12			
Turn-On Delay Time ^c	t _{d(on)}			10	20		
Rise Time ^c	t _r	V_{DD} = 30 V, R_L = 0.6 Ω		15	25	no	
Turn-Off Delay Time ^c	t _{d(off)}	$I_D \cong 50 \text{ A}, V_{GEN}$ = 10 V, R_g = 2.5 Ω		35	50	ns	
Fall Time ^c	t _f			20	30		
Source-Drain Diode Ratings and Cha	aracteristics (T _C = 25 °C)					
Pulsed Current	I _{SM}				60	Α	
Diode Forward Voltage	V _{SD}	$I_F = 20 \text{ A}, V_{GS} = 0 \text{ V}$		1	1.5	V	
Reverse Recovery Time	t _{rr}	I _F = 20 A, di/dt = 100 A/μs		45	100	ns	

Notes:


- a. For design aid only; not subject to production testing.
- b. Pulse test; pulse width \leq 300 µs, duty cycle \leq 2 %.
- c. Independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


服务热线:400-655-8788



TYPICAL CHARACTERISTICS (25 °C unless noted)



Output Characteristics



2- Capacitance (pF) 3000 2400 1800 1300 1200 $\mathsf{C}_{\mathsf{oss}}$ 600


20

C_{iss}

V_{DS} - Drain-to-Source Voltage (V) Capacitance

30

60



Transfer Characteristics



On-Resistance vs. Drain Current



Gate Charge

 $\mathsf{C}_{\mathsf{rss}}$

10

0


0

4800 4200


3600



TYPICAL CHARACTERISTICS (25 °C unless noted)




On-Resistance vs. Junction Temperature




Source-Drain Diode Forward Voltage




THERMAL RATINGS





Maximum Drain Current vs. Ambient Temperature




Normalized Thermal Transient Impedance, Junction-to-Case

服务热线:400-655-8788

5



TO-220AB



DIM.	MILLIN	IETERS	INCHES		
	MIN.	MAX.	MIN.	MAX.	
Α	4.24	4.65	0.167	0.183	
b	0.69	1.02	0.027	0.040	
b(1)	1.14	1.78	0.045	0.070	
С	0.36	0.61	0.014	0.024	
D	14.33	15.85	0.564	0.624	
Е	9.96	10.52	0.392	0.414	
е	2.41	2.67	0.095	0.105	
e(1)	4.88	5.28	0.192	0.208	
F	1.14	1.40	0.045	0.055	
H(1)	6.10	6.71	0.240	0.264	
J(1)	2.41	2.92	0.095	0.115	
L	13.36	14.40	0.526	0.567	
L(1)	3.33	4.04	0.131	0.159	
ØР	3.53	3.94	0.139	0.155	
Q	2.54	3.00	0.100	0.118	
ECN: X15- DWG: 603	0364-Rev. C,	14-Dec-15	•		

Note

• M* = 0.052 inches to 0.064 inches (dimension including protrusion), heatsink hole for HVM

服务热线:400-655-8788



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.