

## CED6426-VB Datasheet

### N-Channel 60 V (D-S) MOSFET

#### PRODUCT SUMMARY

| $V_{DS}$ (V) | $R_{DS(on)}$ ( $\Omega$ ) | $I_D$ (A)       | $Q_g$ (Typ.) |
|--------------|---------------------------|-----------------|--------------|
| 60           | 0.032 at $V_{GS} = 10$ V  | 35 <sup>d</sup> | 21.7         |
|              | 0.037 at $V_{GS} = 4.5$ V | 30 <sup>d</sup> |              |

#### FEATURES



- Halogen-free According to IEC 61249-2-21 Definition
- TrenchFET<sup>®</sup> Power MOSFET
- 100 %  $R_g$  and UIS Tested
- Compliant to RoHS Directive 2002/95/EC



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

#### APPLICATIONS

- Power Supply
  - Secondary Synchronous Rectification
- DC/DC Converter



#### ABSOLUTE MAXIMUM RATINGS $T_C = 25$ °C, unless otherwise noted

| Parameter                                        | Symbol         | Limit                              | Unit |
|--------------------------------------------------|----------------|------------------------------------|------|
| Drain-Source Voltage                             | $V_{DS}$       | 60                                 | V    |
| Gate-Source Voltage                              | $V_{GS}$       | $\pm 20$                           |      |
| Continuous Drain Current ( $T_J = 150$ °C)       | $I_D$          | $T_C = 25$ °C<br>35 <sup>d</sup>   | A    |
|                                                  |                | $T_C = 70$ °C<br>30 <sup>d</sup>   |      |
| Pulsed Drain Current                             | $I_{DM}$       | 100                                |      |
| Avalanche Current                                | $I_{AS}$       | 40                                 |      |
| Single Avalanche Energy <sup>a</sup>             | $E_{AS}$       | 80                                 | mJ   |
| Maximum Power Dissipation <sup>a</sup>           | $P_D$          | $T_C = 25$ °C<br>59.5 <sup>b</sup> | W    |
|                                                  |                | $T_A = 25$ °C <sup>c</sup><br>2.7  |      |
| Operating Junction and Storage Temperature Range | $T_J, T_{stg}$ | - 55 to 150                        | °C   |

#### THERMAL RESISTANCE RATINGS

| Parameter                                    | Symbol     | Limit | Unit |
|----------------------------------------------|------------|-------|------|
| Junction-to-Ambient (PCB Mount) <sup>c</sup> | $R_{thJA}$ | 46    | °C/W |
| Junction-to-Case (Drain)                     | $R_{thJC}$ | 2.1   |      |

Notes:

- Duty cycle  $\leq 1$  %.
- See SOA curve for voltage derating.
- When mounted on 1" square PCB (FR-4 material).
- Package limited.


| SPECIFICATIONS $T_J = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted                          |               |                                                                                                                          |      |       |           |               |
|-----------------------------------------------------------------------------------------------------|---------------|--------------------------------------------------------------------------------------------------------------------------|------|-------|-----------|---------------|
| Parameter                                                                                           | Symbol        | Test Conditions                                                                                                          | Min. | Typ.  | Max.      | Unit          |
| Static                                                                                              |               |                                                                                                                          |      |       |           |               |
| Drain-Source Breakdown Voltage                                                                      | $V_{DS}$      | $V_{DS} = 0\text{ V}, I_D = 250\text{ }\mu\text{A}$                                                                      | 60   |       |           | V             |
| Gate Threshold Voltage                                                                              | $V_{GS(th)}$  | $V_{DS} = V_{GS}, I_D = 250\text{ }\mu\text{A}$                                                                          | 2.0  |       | 3.5       |               |
| Gate-Body Leakage                                                                                   | $I_{GSS}$     | $V_{DS} = 0\text{ V}, V_{GS} = \pm 20\text{ V}$                                                                          |      |       | $\pm 250$ | nA            |
| Zero Gate Voltage Drain Current                                                                     | $I_{DSS}$     | $V_{DS} = 60\text{ V}, V_{GS} = 0\text{ V}$                                                                              |      |       | 1         | $\mu\text{A}$ |
|                                                                                                     |               | $V_{DS} = 60\text{ V}, V_{GS} = 0\text{ V}, T_J = 125\text{ }^{\circ}\text{C}$                                           |      |       | 50        |               |
|                                                                                                     |               | $V_{DS} = 60\text{ V}, V_{GS} = 0\text{ V}, T_J = 150\text{ }^{\circ}\text{C}$                                           |      |       | 250       |               |
| On-State Drain Current <sup>a</sup>                                                                 | $I_{D(on)}$   | $V_{DS} \geq 10\text{ V}, V_{GS} = 10\text{ V}$                                                                          | 50   |       |           | A             |
| Drain-Source On-State Resistance <sup>a</sup>                                                       | $R_{DS(on)}$  | $V_{GS} = 10\text{ V}, I_D = 12\text{ A}$                                                                                |      | 0.032 |           | $\Omega$      |
|                                                                                                     |               | $V_{GS} = 4.5\text{ V}, I_D = 10\text{ A}$                                                                               |      | 0.037 |           |               |
| Forward Transconductance <sup>a</sup>                                                               | $g_{fs}$      | $V_{DS} = 15\text{ V}, I_D = 10\text{ A}$                                                                                |      | 110   |           | S             |
| Dynamic <sup>b</sup>                                                                                |               |                                                                                                                          |      |       |           |               |
| Input Capacitance                                                                                   | $C_{iss}$     | $V_{GS} = 0\text{ V}, V_{DS} = 30\text{ V}, f = 1\text{ MHz}$                                                            |      | 1100  |           | pF            |
| Output Capacitance                                                                                  | $C_{oss}$     |                                                                                                                          |      | 281   |           |               |
| Reverse Transfer Capacitance                                                                        | $C_{rss}$     |                                                                                                                          |      | 130   |           |               |
| Total Gate Charge <sup>c</sup>                                                                      | $Q_g$         | $V_{DS} = 30\text{ V}, V_{GS} = 10\text{ V}, I_D = 10\text{ A}$                                                          |      | 46    |           | nC            |
|                                                                                                     |               | $V_{DS} = 30\text{ V}, V_{GS} = 4.5\text{ V}, I_D = 10\text{ A}$                                                         |      | 28    |           |               |
| Gate-Source Charge <sup>c</sup>                                                                     | $Q_{gs}$      |                                                                                                                          |      | 7     |           |               |
| Gate-Drain Charge <sup>c</sup>                                                                      | $Q_{gd}$      |                                                                                                                          |      | 6.7   |           |               |
| Gate Resistance                                                                                     | $R_g$         | $f = 1\text{ MHz}$                                                                                                       | 0.4  | 2     | 4         | $\Omega$      |
| Turn-On Delay Time <sup>c</sup>                                                                     | $t_{d(on)}$   | $V_{DD} = 30\text{ V}, R_L = 1.5\text{ }\Omega$<br>$I_D \cong 10\text{ A}, V_{GEN} = 10\text{ V}, R_g = 1\text{ }\Omega$ |      | 8     | 16        | ns            |
| Rise Time <sup>c</sup>                                                                              | $t_r$         |                                                                                                                          |      | 9     | 18        |               |
| Turn-Off Delay Time <sup>c</sup>                                                                    | $t_{d(off)}$  |                                                                                                                          |      | 35    | 53        |               |
| Fall Time <sup>c</sup>                                                                              | $t_f$         |                                                                                                                          |      | 9     | 18        |               |
| Drain-Source Body Diode Ratings and Characteristics $T_C = 25\text{ }^{\circ}\text{C}$ <sup>b</sup> |               |                                                                                                                          |      |       |           |               |
| Continuous Current                                                                                  | $I_S$         |                                                                                                                          |      |       | 50        | A             |
| Pulsed Current                                                                                      | $I_{SM}$      |                                                                                                                          |      |       | 100       |               |
| Forward Voltage <sup>a</sup>                                                                        | $V_{SD}$      | $I_F = 10\text{ A}, V_{GS} = 0\text{ V}$                                                                                 |      | 0.75  | 1.5       | V             |
| Reverse Recovery Time                                                                               | $t_{rr}$      | $I_F = 10\text{ A}, dI/dt = 100\text{ A}/\mu\text{s}$                                                                    |      | 34    | 51        | ns            |
| Peak Reverse Recovery Current                                                                       | $I_{RM(REC)}$ |                                                                                                                          |      | 2     | 3         | A             |
| Reverse Recovery Charge                                                                             | $Q_{rr}$      |                                                                                                                          |      | 34    | 51        | nC            |

Notes:


- a. Pulse test; pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$ .  
 b. Guaranteed by design, not subject to production testing.  
 c. Independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


**TYPICAL CHARACTERISTICS** 25 °C, unless otherwise noted




Drain to Source Voltage vs.  $I_D$




On-Resistance vs. Drain Current




Transfer Characteristics









On-Resistance vs. Gate-to-Source Voltage




Transconductance




Gate Charge

**TYPICAL CHARACTERISTICS** 25 °C, unless otherwise noted

**Source-Drain Diode Forward Voltage**

**Threshold Voltage**

**Capacitance**

**Drain Source Breakdown vs. Junction Temperature**

**On-Resistance vs. Junction Temperature**

**Current Derating**


**TYPICAL CHARACTERISTICS** 25 °C, unless otherwise noted



Single Pulse Avalanche Current Capability vs. Time




\*  $V_{GS} >$  minimum  $V_{GS}$  at which  $R_{DS(on)}$  is specified  
**Safe Operating Area**



Normalized Thermal Transient Impedance, Junction-to-Case

TO-251AA (DPAK)



Note: Dimension L3 is for reference only.

| Dim                            | MILLIMETERS |      | INCHES    |       |
|--------------------------------|-------------|------|-----------|-------|
|                                | Min         | Max  | Min       | Max   |
| A                              | 2.21        | 2.38 | 0.087     | 0.094 |
| A1                             | 0.89        | 1.14 | 0.035     | 0.045 |
| b                              | 0.71        | 0.89 | 0.028     | 0.035 |
| b1                             | 0.76        | 1.14 | 0.030     | 0.045 |
| b2                             | 5.23        | 5.43 | 0.206     | 0.214 |
| c                              | 0.46        | 0.58 | 0.018     | 0.023 |
| c1                             | 0.46        | 0.58 | 0.018     | 0.023 |
| D                              | 5.97        | 6.22 | 0.235     | 0.245 |
| E                              | 6.48        | 6.73 | 0.255     | 0.265 |
| e                              | 2.28 BSC    |      | 0.090 BSC |       |
| L                              | 8.89        | 9.53 | 0.350     | 0.375 |
| L1                             | 1.91        | 2.28 | 0.075     | 0.090 |
| L2                             | 0.89        | 1.27 | 0.035     | 0.050 |
| L3                             | 1.15        | 1.52 | 0.045     | 0.060 |
| ECN: S-03946—Rev. E, 09-Jul-01 |             |      |           |       |
| DWG: 5346                      |             |      |           |       |

# Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

## Material Category Policy

**Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)**

**Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.**

**Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.**