






Aug.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT




RECOMMENDED PCB PATTERN (FREE)
(PCB THICKNESS:t=1.6mm, METAL MASK THICKNESS:t=0.15mm)



NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM

- : IR IN THE AIR OR NITROGEN
- NO. OF CYCLES : 2 MAX
- PEAK : 250°C
- OVER 230°C : 20~40s
- PREHEAT : 150~180°C
- 90~120s

- 2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
- 3. CO-PLANARITY SHALL BE 0.1mm MAX.
- 4. RECOMMENDED PCB THICKNESS IS 1.6mm.
FOR PCB WITH A THICKNESS OF 1.6 OR GREATER,
THERE IS NO PROTRUS CONNECTOR ON THE UNDERSIDE OF THE BOARD.
WHEN USING PCB WITH A THICKNESS OF LESS THAN 1.6,
THE CONNECTOR PROTRUDES BELOW THE PCB.
- 5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




2	BRASS	SURFACE : TIN PLATING 1μm min					
2	BRASS	UNDER : NICKEL PLATING 1μm min	3	BRASS	SURFACE : TIN PLATING 1μm min		
1	PA	BLACK UL94V-0	3	BRASS	UNDER : NICKEL PLATING 1μm min		
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS
UNITS	mm	SCALE	2:1	COUNT	3	DESCRIPTION OF REVISIONS	DIS-T-00019459
DESIGNED		YANG CHUANXING		CHECKED		MASAHIRO SHOUJI	
DATE		20231102		APPROVED		MASAHIRO SHOUJI 20230427	
DRAWING NO.		EDC-402619-00-00		CHECKED		MASAHIRO SHOUJI 20230427	
PART NO.		ZG05HV-6P-3.3H		DESIGNED		YANG CHUANXING 20230427	
CODE NO.		CL0754-2112-0-00		DRAWN		YANG CHUANXING 20230427	


Aug.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKING STYLE

REEL DIMENSION (FREE)




PACKING STYLE DRAWING



300PCS/REEL

CARDBOARD DIMENSION (FREE)

W=(405) (mm)
 D=(405) (mm)
 H=(51) (mm)



HRS	DRAWING NO.	EDC-402619-00-00	2/2
	PART NO.	ZG05HV-6P-3.3H	
	CODE NO.	CL0754-2112-0-00	