

90N04-VB TO252 Datasheet N-Channel 40-V (D-S) MOSFET

PRODUCT SUMMARY					
V _{DS} (V)	$R_{DS(on)}$ (Ω)	I _D (A) ^{a, c}	Q _g (Typ.)		
40	0.0050 at $V_{GS} = 10 \text{ V}$	85	80 nC		
40	0.0065 at V _{GS} = 4.5 V	70	00 HC		


FEATURES

- TrenchFET® Power MOSFET
- 100 % R_g and UIS Tested



APPLICATIONS

- Synchronous Rectification
- Power Supplies



N-Channel MOSFET

TO-252						
~		٦				
F		——————————————————————————————————————				
	_					
	\bigcirc					
屽	$\overline{}$,				
	ш					
	_					
G	D	S				

ABSOLUTE MAXIMUM RATINGS	Γ _A = 25 °C, unle	ss otherwise no	oted	
Parameter	Symbol	Limit	Unit	
Drain-Source Voltage	V_{DS}	40	V	
Gate-Source Voltage		V_{GS}	± 25	V
	T _C = 25 °C		85 ^{a, c}	
Continuous Proin Current /T 475 °C)	T _C = 70 °C	,	70 ^c	
Continuous Drain Current (T _J = 175 °C)	T _A = 25 °C	I _D	59 ^b	,
	T _A = 70 °C		53 ^b	A
Pulsed Drain Current		I _{DM}	250	
Avalanche Current Pulse L = 0.1 mH		I _{AS}	80	
Single Pulse Avalanche Energy	L=0.1 mn	E _{AS}	320	mJ
Continuous Source-Drain Diode Current	T _C = 25 °C	La	110 ^{a, c}	^
Continuous Source-Diam Diode Current	T _A = 25 °C	I _S	2.6 ^b	Α
	T _C = 25 °C		312 ^a	
Maximum Barran Dissipation	T _C = 70 °C	P _D	200	\A/
Maximum Power Dissipation	T _A = 25 °C	FD F	3.13 ^b	W
	T _A = 70 °C		2.0 ^b	
Operating Junction and Storage Temperature Range	T _J , T _{stg}	- 55 to 150	°C	

THERMAL RESISTANCE RATINGS						
Parameter		Symbol	Typical	Maximum	Unit	
Maximum Junction-to-Ambient ^b	Steady State	R _{thJA}	32	40	°C/W	
Maximum Junction-to-Case	Steady State	R_{thJC}	0.33	0.4	C/VV	

Notes:

- a. Based on $T_C = 25$ °C.
- b. Surface Mounted on 1" x 1" FR4 board.
- c. Calculated based on maximum junction temperature. Package limitation current is 110 A.



Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$	40			V	
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	I _D = 250 μA		41		mV/°C	
V _{GS(th)} Temperature Coefficient	$\Delta V_{GS(th)}/T_J$	10 = 200 μΛ		- 8		IIIV/ C	
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	1.2		2.5	V	
Gate-Source Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 100	nA	
Zoro Coto Voltago Drain Current	l	$V_{DS} = 40 \text{ V}, V_{GS} = 0 \text{ V}$			1		
Zero Gate Voltage Drain Current	I _{DSS}	$V_{DS} = 40 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 55 ^{\circ}\text{C}$			10	μA	
On-State Drain Current ^a	I _{D(on)}	$V_{DS} \ge 5 \text{ V}, V_{GS} = 10 \text{ V}$	120			Α	
David Common Con Otata Basista and	D	V _{GS} = 10 V, I _D = 30 A		0.0050			
Drain-Source On-State Resistance ^a	R _{DS(on)}	$V_{GS} = 4.5 \text{ V}, I_D = 20 \text{ A}$		0.0065		Ω	
Forward Transconductance ^a	9 _{fs}	V _{DS} = 15 V, I _D = 30 A		180		S	
Dynamic ^b							
Input Capacitance	C _{iss}			2380			
Output Capacitance	C _{oss}	$V_{DS} = 20 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		550		pF	
Reverse Transfer Capacitance	C _{rss}			250			
Total Gate Charge	Q_g			80	120	nC	
Gate-Source Charge	Q _{gs}	$V_{DS} = 20 \text{ V}, V_{GS} = 10 \text{ V}, I_{D} = 20 \text{ A}$		20			
Gate-Drain Charge	Q _{gd}			12			
Gate Resistance	R _g	f = 1 MHz		0.85	1.3	Ω	
Turn-On Delay Time	t _{d(on)}			20	30		
Rise Time	t _r	V_{DD} = 20 V, R_L = 1.0 Ω		11	17		
Turn-Off Delay Time	t _{d(off)}	$I_D\cong 20$ A, V_{GEN} = 10 V, R_g = 1 Ω		77	115		
Fall Time	t _f			10	15		
Turn-On Delay Time	t _{d(on)}			102	155	ns	
Rise Time	t _r	V_{DD} = 20 V, R_L = 1.0 Ω		62	95		
Turn-Off Delay Time	t _{d(off)}	$I_D \cong 20 \text{ A}, V_{GEN} = 4.5 \text{ V}, R_g = 1 \Omega$		180	270	1	
Fall Time	t _f			60	90		
Drain-Source Body Diode Characteristic	s					1	
Continuous Source-Drain Diode Current	Is	T _C = 25 °C			110	۸	
Pulse Diode Forward Current ^a	I _{SM}				200	A	
Body Diode Voltage	V _{SD}	I _S = 20 A		0.8	1.2	V	
Body Diode Reverse Recovery Time	t _{rr}			50	75	ns	
Body Diode Reverse Recovery Charge	Q _{rr}	1 20 A di/d+ 100 A/vo T 25 °C		70	105	nC	
Reverse Recovery Fall Time	t _a	$I_F = 20 \text{ A}, \text{ di/dt} = 100 \text{ A/}\mu\text{s}, T_J = 25 ^{\circ}\text{C}$		30			
Reverse Recovery Rise Time	t _b	_		20		ns	


Notes:

- a. Pulse test; pulse width $\leq 300~\mu s,$ duty cycle $\leq 2~\%.$
- b. Guaranteed by design, not subject to production testing.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted







TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



On-Resistance vs. Junction Temperature



On-Resistance vs. Gate-to-Source Voltage



Forward Diode Voltage vs. Temperature



Threshold Voltage




* V_{GS} > minimum V_{GS} at which $R_{DS(on)}$ is specified

Safe Operating Area, Junction-to-Ambient



TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted






* The power dissipation P_D is based on $T_{J(max)}$ = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.




Normalized Thermal Transient Impedance, Junction-to-Case



TO-252AA CASE OUTLINE







	MILLIMETERS		INCHES		
DIM.	MIN.	MAX.	MIN.	MAX.	
Α	2.18	2.38	0.086	0.094	
A1	-	0.127	-	0.005	
b	0.64	0.88	0.025	0.035	
b2	0.76	1.14	0.030	0.045	
b3	4.95	5.46	0.195	0.215	
С	0.46	0.61	0.018	0.024	
C2	0.46	0.89	0.018	0.035	
D	5.97	6.22	0.235	0.245	
D1	5.21	=	0.205	=	
Е	6.35	6.73	0.250	0.265	
E1	4.32	=	0.170	-	
Н	9.40	10.41	0.370	0.410	
е	2.28 BSC		0.090 BSC		
e1	4.56 BSC		0.180 BSC		
L	1.40	1.78	0.055	0.070	
L3	0.89	1.27	0.035	0.050	
L4	-	1.02	-	0.040	
L5	1.14	1.52	0.045	0.060	
ECN: X12-0247-Rev. M, 24-Dec-12					


Note

DWG: 5347

• Dimension L3 is for reference only.



RECOMMENDED MINIMUM PADS FOR DPAK (TO-252)



Recommended Minimum Pads Dimensions in Inches/(mm)



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.