


Features

- Low $R_{DS(on)}$ @ $V_{GS}=10V$
- 5V Logic Level Control
- N Channel SOP8 Package
- Pb-Free, RoHS Compliant

$V_{(BR)DSS}$	$R_{DS(ON)}\text{ Typ}$	$I_D \text{ Max}$
30V	8.2mΩ @ 10V	15A
	11.5mΩ @ 4.5V	

Applications

- High-Speed Switching
- General Purpose Applications
- Power Management Applications
- Load Switch
- Hand-Held Instruments


Order Information
SOP8

Product	Package	Marking	Packing
DWS009N03	SOP8	009N03	4000PCS/Reel

Absolute Maximum Ratings

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Symbol	Parameter	Rating	Unit
Common Ratings ($T_j=25^\circ C$ Unless Otherwise Noted)			
V_{GS}	Gate-Source Voltage	± 20	V
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	30	V
$T_{J, STG}$	Junction and Storage Temperature Range	-50 to 150	°C
Mounted on Large Heat Sink			
I_{DM}	Pulse Drain Current Tested①	$T_A=25^\circ C$	60
I_D	Continuous Drain Current	$T_A=25^\circ C$	15
		$T_A=70^\circ C$	12
P_D	Maximum Power Dissipation	$T_A=25^\circ C$	3.1
R_{JA}	Maximum Junction-to-Ambient		40 °C/W

Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise stated)						
$V_{(\text{BR})\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}$, $I_D=250\mu\text{A}$	30	--	--	V
I_{DSS}	Zero Gate Voltage Drain Current($T_A=25^\circ\text{C}$)	$V_{\text{DS}}=30\text{V}$, $V_{\text{GS}}=0\text{V}$	--	--	1	μA
	Zero Gate Voltage Drain Current($T_A=125^\circ\text{C}$)	$V_{\text{DS}}=24\text{V}$, $V_{\text{GS}}=0\text{V}$	--	--	100	μA
I_{GSS}	Gate-Body Leakage Current	$V_{\text{GS}}=\pm 20\text{V}$, $V_{\text{DS}}=0\text{V}$	--	--	± 100	nA
$V_{\text{GS}(\text{TH})}$	Gate Threshold Voltage	$V_{\text{DS}}=V_{\text{GS}}$, $I_D=250\mu\text{A}$	1.0	1.8	2.5	V
$R_{\text{DS}(\text{ON})}$	Drain-Source On-State Resistance②	$V_{\text{GS}}=10\text{V}$, $I_D=10\text{A}$	--	8.2	10	$\text{m}\Omega$
$R_{\text{DS}(\text{ON})}$	Drain-Source On-State Resistance②	$V_{\text{GS}}=4.5\text{V}$, $I_D=5\text{A}$	--	11.5	15	$\text{m}\Omega$
Dynamic Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise stated)						
C_{iss}	Input Capacitance	$V_{\text{DS}}=15\text{V}$, $V_{\text{GS}}=0\text{V}$, $f=1\text{MHz}$	--	804	--	pF
C_{oss}	Output Capacitance		--	129	--	pF
C_{rss}	Reverse Transfer Capacitance		--	95	--	pF
R_g	Gate Resistance	$f=1\text{MHz}$		3.7		Ω
Q_g	Total Gate Charge	$V_{\text{DS}}=15\text{V}$, $I_D=20\text{A}$, $V_{\text{GS}}=10\text{V}$	--	15.6	--	nC
Q_{gs}	Gate Source Charge		--	3	--	nC
Q_{gd}	Gate Drain Charge		--	4.1	--	nC
Switching Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise stated)						
$t_{\text{d}(\text{on})}$	Turn on Delay Time	$V_{\text{DD}}=15\text{V}$, $I_D=1\text{A}$, $R_C=3.3\Omega$, $V_{\text{GS}}=10\text{V}$	--	6.5	--	ns
t_r	Turn on Rise Time		--	3	--	ns
$t_{\text{d}(\text{off})}$	Turn Off Delay Time		-	20	--	ns
t_f	Turn Off Fall Time		--	5.2	--	ns
Source Drain Diode Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise stated)						
I_{SD}	Source drain current(Body Diode)	$T_A=25^\circ\text{C}$	--	--	4	A
V_{SD}	Forward on voltage②	$T_J=25^\circ\text{C}$, $I_{\text{SD}}=5\text{A}$, $V_{\text{GS}}=0\text{V}$	--	0.78	1.2	V

Notes: ① Pulse width limited by maximum allowable junction temperature

②Pulse width $\leq 300\mu\text{s}$; duty cycles $\leq 2\%$.

Typical Characteristics




Fig1. Typical Output Characteristics




Fig2. $V_{GS(TH)}$ Voltage Vs. Temperature




Fig3. Typical Transfer Characteristics




Fig4. On-Resistance vs. Drain Current and Gate




Fig5. Typical Source-Drain Diode Forward Voltage




Fig6. Maximum Safe Operating Area

Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance




Fig10. Switching Time Test Circuit and waveforms





Fig11. Unclamped Inductive Test Circuit and waveforms

SOP8 Mechanical Data

DIMENSIONS (unit : mm)

Symbol	Min	Typ	Max	Symbol	Min	Typ	Max
A	--	1.75	--	A₁	0.10	0.18	0.25
A₂	1.25	1.35	1.45	A₃	--	0.25	--
b_p	0.36	0.42	0.49	c	0.19	0.22	0.25
D	4.80	4.92	5.00	E	3.80	3.90	4.00
e	--	1.27	--	H_E	5.80	5.98	6.20
L	--	1.05	--	L_p	0.40	0.68	1.00
Q	0.60	0.65	0.70	v	--	0.25	--
w	--	0.25	--	y	--	0.10	--
Z	0.30	0.50	0.70	θ	0°		8°

Legal Disclaimer

The Dowell Technology given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Dowell Technology hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Dowell Technology Office (www.dowellsemi.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Dowell Technology Office. Dowell Technology components may be used in life-support devices or systems only with the express written approval of Dowell Technology, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.