

Features

- Low operating voltage: 24V
- Ultra low capacitance: 25pF(Typ)
- Ultra low leakage: nA level
- Low clamping voltage
- -IEC 61000-4-2 (ESD) immunity test
 Air discharge: $\pm 30\text{kV}$
 Contact discharge: $\pm 30\text{kV}$
- -IEC61000-4-4 (EFT) 40A (5/50ns)
- 3-pin leadless package
- These are Pb-Free Devices
- Response Time is Typically $< 1\text{ ns}$


Mechanical Characteristics

- Package: SOT-23
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound
- Terminal Connections: See Diagram Below
- -IEC 61000-4-2 (ESD) immunity test

Applications

- Industrial Controls
- Personal Digital Assistants
- Notebooks and Handhelds
- CAN Bus Protection
- Automotive Appllcatrons

Dimensions and Pin Configuration



SOT-23

MARKING: 27E *

27E= Device code

*** =Month code**


Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	300	W
IEC 61000-4-2 Spec Current at 60 ns (A)	Ipp	7	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD	±30 ±30	KV
Operating Temperature Range	TJ	-55 to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C

Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	VRWM	--	--	24	V	
Breakdown Voltage	VBR	26.7	--	--	V	IT= 1mA
Reverse Leakage Current	IR	--	--	0.08	uA	VRWM=24V
Clamping Voltage	VC	--	33	--	V	Ipp=1A(8x 20us pulse)
Clamping Voltage	VC	--	--	43	V	Ipp=7A(8x 20us pulse)
Junction Capacitance	CJ	--	25	--	pF	VR =0V, f =1MHz, Pin1 to Pin2

Symbol	Parameter
VRWM	Nominal Reverse Working Voltage
IR	Reverse Leakage Current @ VRWM
VBR	Reverse Breakdown Voltage @ IT
IT	Test Current for Reverse Breakdown
VC	Clamping Voltage @ IPP
IPP	Maximum Peak Pulse Current
CESD	Parasitic Capacitance
VR	Reverse Voltage
f	Small Signal Frequency



Characteristic Curves

Fig1. 8/20 μ s Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve



Package Outline Dimensions (unit: mm)

SOT-23



Mounting Pad Layout (unit: mm)

