

	1	2	3	4	5	6	7	8	9																																																																					
G	RoHS																																																																													
F	SPECIFICATIONS Rated Current:3.0AMP Contact Resistance:20mΩ Max Withstand Voltage:1000V AC/DC Insulation Resistance:1000MΩ Min Operation Temperature:-40℃ to +105℃				Recommended P.C.B Layout(Top Side) (PCB BOARD TOLERANCE±0.05)																																																																									
E	Contact Material:Brass Contact Plating:Au Over Ni Insulator Material:Polyester(UL94V-0) Standard: PA6T Max.Processing Temp: 230℃ for 30-60 seconds (260℃ for 10 seconds)																																																																													
D																																																																														
C						<table><tr><th colspan="6">Dimension antitheses list</th></tr><tr><th>ITEM</th><th>PB</th><th>PC</th><th>PW</th><th>H</th><th>W</th></tr><tr><td>001</td><td>9.0</td><td></td><td>7.1</td><td>8.5</td><td>5.0</td></tr><tr><td>002</td><td></td><td></td><td></td><td></td><td></td></tr></table>				Dimension antitheses list						ITEM	PB	PC	PW	H	W	001	9.0		7.1	8.5	5.0	002																																																		
Dimension antitheses list																																																																														
ITEM	PB	PC	PW	H	W																																																																									
001	9.0		7.1	8.5	5.0																																																																									
002																																																																														
B																																																																														
A	<table><tr><td></td><td></td><td></td><td></td><td colspan="2">OPERATION</td><td rowspan="2">DRAW</td><td></td><td></td><td>SCALE</td><td>FIT</td><td rowspan="5">深圳市连盛精密连接器有限公司</td></tr><tr><td></td><td></td><td></td><td></td><td>X.X</td><td>±0.30</td><td></td><td></td><td>UNIT</td><td>mm</td></tr><tr><td></td><td></td><td></td><td></td><td>X.XX</td><td>±0.20</td><td rowspan="2">CHECK</td><td></td><td></td><td>SIZE</td><td>A4</td></tr><tr><td>A0</td><td>2012.03.28</td><td colspan="2">NEW DRAWING</td><td>X.XXX</td><td>±0.10</td><td></td><td></td><td>SHEET</td><td>1/1</td></tr><tr><td>REV</td><td>DATE</td><td colspan="2">MODIFICATION DESCRIPTION</td><td>CHANGE</td><td>Angle</td><td>±3°</td><td rowspan="2">APPROVE</td><td></td><td></td><td>PROJ.</td><td>◆</td><td>PART NO.</td><td>1020300648</td></tr><tr><td></td><td></td><td colspan="2"></td><td></td><td>DIM</td><td>TOL</td><td></td><td></td><td>TITLE:</td><td colspan="2">2.54FH H=8.5 W=5.0 2*2P SMT=7.1 总高9.0 U型 AU1U 青铜 PA6T</td></tr></table>									OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司					X.X	±0.30			UNIT	mm					X.XX	±0.20	CHECK			SIZE	A4	A0	2012.03.28	NEW DRAWING		X.XXX	±0.10			SHEET	1/1	REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle	±3°	APPROVE			PROJ.	◆	PART NO.	1020300648						DIM	TOL			TITLE:	2.54FH H=8.5 W=5.0 2*2P SMT=7.1 总高9.0 U型 AU1U 青铜 PA6T					
				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司																																																																			
				X.X	±0.30				UNIT	mm																																																																				
				X.XX	±0.20	CHECK			SIZE	A4																																																																				
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10				SHEET	1/1																																																																				
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle	±3°	APPROVE			PROJ.		◆	PART NO.	1020300648																																																																
					DIM	TOL				TITLE:	2.54FH H=8.5 W=5.0 2*2P SMT=7.1 总高9.0 U型 AU1U 青铜 PA6T																																																																			
	1	2	3	4	5	6	7	8	9																																																																					