


- 1、插入力: 2.94~29.4N(0.3~3.0kgf)
- 2、拔出力: 2.94~29.4N(0.3~3.0kgf)
- 3、接触电阻: $\leq 30m\Omega$
- 4、绝缘电阻: $>100M\Omega$ DC 500V
- 5、耐电压: AC 500V 1min无飞弧及击穿
- 6、寿命: 5000 10~20次/min
- 7、额定负载: DC 12V 1A



The diagram shows a test tube on the left and a circuit diagram on the right. The circuit consists of a battery (represented by two cells), a switch, and a bell. The switch is currently open, and the bell is shown with a bell-shaped component.

序号	零件料号	名称	材料	数量	镀层/颜色	备注
1		密封件	PPA	1PCS	黑色	
2	2号脚	平片	磷铜0.3	1PCS	Ag	
3	3号脚	触片	磷铜0.3	1PCS	Ag	
4	4号脚	弹片	磷铜0.3	1PCS	Ag	
5		PIN	铜针	1PCS	TX	
6						

 韩下® 深圳市韩下电子有限公司 HANXIA				1. 单位 X.X ±0.15 X.X ±0.10 X.XX ±0.05		2. 公差 XX' ±3° X' ±2° X.X' ±1°	
设计	黄彬	日期	2020.5.14	品名	DC座		
审核	张伟	日期	2020.5.14	型号	HX DC044-2.0 TP		
批准	罗小春	单位	工程部	页码	1P1	A4	



深圳市韩下电子有限公司

Shenzhen Hanxia Electronic Co., Ltd

Tel: 0755-33819206 Fax: 0755-27597491

承 认 书

SPECIFICATION FOR APPROVAL

客 户 Customer:

产品名称 Project:

DC座

规格型号 Part No:

HX DC044-2.0 TP

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	



深圳市韩下电子有限公司

品名 (NAME) : DC座

型号 (MODEL) : HX DC044-2.0 TP

1.溫度5~35℃, 湿度45~85%標準狀態下測試。

In normal fettle to test.Temperature 5~35℃ and humidity 45~85%

2.溫度-30~70℃環保內使用。

In entironment of remperature -30~70℃

ITEM 專案

TEST CONDITION 測試條件

SPECIFICICAION 規格

3.ELECTRONICAL RESISTAN 電氣性能

3.1	CONTACT RESISANCE 接觸阻抗	Being measured at 1KHZsmall current connect resistance meter.在1KHZ小電流下測量。	0.03歐姆以下
3.2	INSULATION RESISTANCE 絕緣阻抗	Measurements shall be made following application of DC500V poten rial across terminals and across terminals and frame for 1 minute.在端子之間和端子與殼之間加DC500V條件下，持續1分鐘測量。	100M min 100兆歐以上。
3.3	WITHSTAND VOLTAGE 耐電壓	AC500V(50HZ or 60HZ) shall be applied across terminals and across terminals and frame for one minute.在端子之間和端子與殼之間加AC500V條件下，持續1分鐘測量。	There shall be no breakdown 無擊穿現象。

4.MECHANICAL CHARACTERISTICS 機械性能

4.1	INSERION AND WITHDRAW 插拔力	Being measure at across spring piece and across matching plug for ergo meter. 用測力計在插頭與彈片之間進行測試	Insertion and extraction force 2.94~29.4N, 插拔力2.94~29.4N
4.2	TERMINAL STRENGTH 端子強度	A static force of 500gf being applied in one directionon the top of terminal for 1 minute.一個500克之靜負荷施加於端子頂部的一個方向持續1分鐘。	There shall be no sign of damage mechanical and electrically. 無任何迹象顯示機械及電器性能之損壞。



5. DURABILTY 耐 久 性

5. 1	SOLDERING TEST 可焊性試驗	The top of terminals shall be dipped 2mm in the loder bath at a temperature of 230: 5°C for 3sec. 端子頂部被浸入焊池2mm深，溫度230±5°C時間3秒	A new un form coating of shall cover above 75 % of the surface being immersed. 浸入的部分75%以上表面將被錫覆蓋。
5. 2	LIFE TEST 壽命試驗	5000 cycles of operation at rate of 20-30 cycles per minture with unloading. 無負載條件下，每分鐘20—30次的速度操作5000次。	(1) Contact resistance.40mΩ max 接觸阻抗40毫歐以下 (2) Drive fore 30 inital value 動作力變化範圍初始值30 (3) ITEM專案—3.2 (4) ITEM專案—3.3 (5) INEM—4.2
5. 3	HEAT TEST 耐熱試驗	80: 2°C for 48 hours after test keep in normal condition for 30minutes. 在80±2°C環境中放48小時，再放在正常環境中30分鐘後進行測試。	(1) Contact resistance 50mΩ max.接觸电阻50毫欧以下
5. 4	HUMIDITY TEST 耐濕試驗	The condition of temperature 40±2-°C and humidity 90-95 %for 48 hours after test keep in normal condition for 30 min.在40±2-°C 90—95 % Rh環境中放48小時，再放在正常環境中30分鐘後進行測試。	(2) Insulation resistance 100MΩ min.绝缘电阻100M欧以上 (3) There shall be no sign of damage mechanically and electrically.無任何迹象顯示機械及電器性能之損壞。
5. 5	COLD TEST 耐冷試驗	At—30±2-°C for 48 hours ,after test keep in normal condition for 30 min.在—30 ± 2-°C環境中放48小時，再置於正常環境中30分鐘後進行測試。	