



2~3孔两边第一根针打K,  
其余孔位两边第二根针打K



PCB LAYOUT

SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 100V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 10mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 800V AC/minute
7. Material: Wafer PA66 UL94-V0(2)  
PIN Brass Tin-plated

| Circuit | Part NO.       | Dimensions mm |       |       |
|---------|----------------|---------------|-------|-------|
|         |                | A             | B     | C     |
| 2       | HC-PH-2A-K-10  | 2.00          | 5.90  | 4.70  |
| 3       | HC-PH-3A-K-10  | 4.00          | 7.90  | 6.70  |
| 4       | HC-PH-4A-K-10  | 6.00          | 9.90  | 8.70  |
| 5       | HC-PH-5A-K-10  | 8.00          | 11.90 | 10.70 |
| 6       | HC-PH-6A-K-10  | 10.00         | 13.90 | 12.70 |
| 7       | HC-PH-7A-K-10  | 12.00         | 15.90 | 14.70 |
| 8       | HC-PH-8A-K-10  | 14.00         | 17.90 | 16.70 |
| 9       | HC-PH-9A-K-10  | 16.00         | 19.90 | 18.70 |
| 10      | HC-PH-10A-K-10 | 18.00         | 21.90 | 20.70 |
| 11      | HC-PH-11A-K-10 | 20.00         | 23.90 | 22.70 |
| 12      | HC-PH-12A-K-10 | 22.00         | 25.90 | 24.70 |
| 13      | HC-PH-13A-K-10 | 24.00         | 27.90 | 26.70 |
| 14      | HC-PH-14A-K-10 | 26.00         | 29.90 | 28.70 |
| 15      | HC-PH-15A-K-10 | 28.00         | 31.90 | 30.70 |
| 16      | HC-PH-16A-K-10 | 30.00         | 33.90 | 32.70 |

Ordering Information

HC-PH - N\*\*\* - \* - \* - 10

Pin Type Colour 默认=无脚  
 V=孔座 A=直针 B=红色 K=带引脚  
 M=弯针 L=蓝色  
 AW=定位弯针 P=紫色  
 V=绿色  
 PF=增强-本色

|           |                        |                   |                  |       |                   |  |                                                           |  |              |     |
|-----------|------------------------|-------------------|------------------|-------|-------------------|--|-----------------------------------------------------------|--|--------------|-----|
|           |                        |                   | GENREL TOLERANCE |       | 制 图<br>DRAWING    |  | 深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianluELECTRONICS CO., LTD |  |              |     |
|           |                        |                   | DIM              | TOL   | 审 核<br>CHECK      |  | 产品名称<br>TITLE                                             |  | 版本<br>REV.   | A   |
|           |                        |                   | X. X             | ±0.30 | 批 准<br>APPROVAL   |  | PH (2.00)单排 直针<br>(带K脚)                                   |  | 单 位<br>UNITS | mm  |
| 1         |                        |                   | X. XX            | ±0.20 | 比 例<br>SCALE      |  | 产品料号<br>PART NO.                                          |  | 页 次<br>SHEET | 1/1 |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE | X. XXX           | ±0.10 | 投 影<br>Projection |  | 材 料<br>MATERIAL                                           |  |              |     |
|           |                        |                   | Angle            | ±3.0° |                   |  |                                                           |  |              |     |