



佛山市国星光电股份有限公司

FOSHAN NATIONSTAR OPTOELECTRONICS CO., LTD

产品规格书

SPECIFICATION

顾客名称 Customer		产品名称 Product	Chip LED
顾客型号 Customer Type		产品型号 Type	NCD0603R1B1-F
顾客部品号 Customer No.		版本号 Version NO	A 版



地址: 广东省佛山市禅城区华宝南路18号

Add: NO.18 South Huabao Rd, Foshan, Guangdong, China

电话 (Tel): 0757-82100219

传真 (Fax): 0757-82100220

邮编 (Zip): 528000

邮箱 (Email): chipLED@nationstar.com

<http://www.nationstar.com>

研发中心 Research & Development Center			客户 (加盖公章) Customer (Stamp)
制定 DRAW	审核 CHECK	批准 APPROVE	确认 CONFIRM
李萍	陆紫珊	朱明军	
发放日期 (Release Date): 2024-06-29			

NCD0603R1B1-F

Chip Light Emitting Diode

技术数据表 Technical Data Sheet

本产品主要作为信号指示及照明的电子元件, 广泛应用于各类使用表面贴装结构的电子产品中, 如家用电器的开关指示灯、手机键盘灯、汽车仪表盘指示灯等。

This product is generally used as indicator and luminance for surface mounted electronic equipment, such as household appliance, communication equipment, and dashboard.

特性:

➤ 管芯材料:

Material:

红色 Red

蓝色 Blue

AlGaInP

InGaN

Features:

➤ 封装材料: 环氧树脂

Encapsulation: Epoxy Resin

➤ 焊接方法: 无铅回流焊

Soldering methods: Pb-Free reflow soldering

➤ 光强高, 功耗低, 可靠性好, 寿命长

High Luminous Intensity ,Low Power Dissipation, Good Reliability and Long Lifespan

➤ 符合欧盟公布的 ROHS 指令要求

Complied With ROHS Directive








* 产品规格如因工艺改进而有所改变, 恕不另行通知。

* The specifications of the product may be modified for improvement without notice.

外形尺寸

Outline Dimension



敷铜区域:
Cuprum Area: 
阻焊丝印区域:
Solder Resist: 
*无特别规定时, 公差:±0.1mm
*The Tolerances Unless Mentioned is:±0.1mm

光电参数 (1)

Electro-Optical Characteristics(1)

✧ 极限参数 (温度=25℃)
Absolute Maximum Ratings (Temperature=25℃)

参数名称 Parameter	符号 Symbol	数值 Rating	单位 Unit
正向电流 Forward Current	IF	20	mA
正向脉冲电流* Pulse Forward Current*	IFP	50	mA
反向电压 Reverse Voltage	VR	5	V
工作温度 Operating Temperature	TOPR	-30 ~ +85	℃
贮存温度 Storage Temperature	Tstg	-40 ~ +100	℃
功耗 Power Dissipation	R	52	mW
	B	72	

* 注：脉冲宽度≤0.1ms，占空比≤1/10 * Note: Pulse Width≤0.1ms, Duty≤1/10

✧ 光电参数 (温度=25℃)
Electro-Optical Characteristics (Temperature=25℃)

参数名称 Parameter	符号 Symbol	条件 Condition	颜色 Color	最小值 Min.	典型值 Typ.	最大值 Max.	单位 Unit
反向电流 Reverse Current	I _R	V _R =5	R	-	-	10	μA
			B	-	-	10	
正向电压 Forward Voltage	V _F	I _F =20mA	R	1.6	2.0	2.6	V
			B	2.6	3.2	3.6	
主波长 Dominant Wavelength	λ _D		R	617	625	632	nm
			B	460	467	475	
半波宽度 Spectrum Radiation Bandwidth	Δλ		R	-	15	-	nm
			B	-	22	-	
光强 Luminous Intensity	I _V		R	45	80	135	mcd
			B	65	120	195	
视角度 View Angle	2θ _{1/2}	-	-	-	140	-	deg.

* 注 1：光强偏差±15%；压降偏差±0.1V；(X,Y)坐标偏差±0.01；单色光波长偏差±1nm；视角偏差±10°。

* Note1: Tolerance on each Luminous Intensity bin is ±15%; Tolerance on each Forward Voltage bin is ±0.1V; Tolerance on each Hue(X,Y) bin is ±0.01; Tolerance of Dominant Wavelength ±1nm; Tolerance of View Angle ±10°.

* 注 2：以上参数仅供参考，请以实物标签为准。我司给出的参数均由国星测试系统测得。

* Note2: The parameters above are only for your reference. In case of any discrepancy, please adhere to the label of our actual products. All parameters are tested by the standard testing system of NationStar.

光电参数 (2)

Electro-Optical Characteristics(2)

✧ 正向电压 (温度=25℃, 测试电流=20 mA)

Forward Voltage (Ta=25℃,IF=20mA)

典型电压档范围 Voltage Classification Range		
V _F (V)	R	B
	1.6-1.8	2.6-2.8
	1.8-2.0	2.8-3.0
	2.0-2.2	3.0-3.2
	2.2-2.4	3.2-3.4
	2.4-2.6	3.4-3.6

✧ 光强 (温度=25℃, 测试电流=20 mA)

Luminous Intensity (Ta=25℃,IF=20mA)

典型光强档范围 Luminous Classification Range		
I _v (mcd)	R	B
	45-65	65-95
	65-95	95-135
	95-135	135-195







✧ 主波长 (温度=25℃, 测试电流=20 mA)

Dominant Wavelength (Ta=25℃,IF=20mA)

典型波长档范围 Dominant Wavelength Range		
λ _d (nm)	R	B
	617-622	460-465
	622-627	465-470
	627-632	470-475

典型特性曲线

Typical Characteristics Curves



可靠性试验

Reliability Test Items And Conditions

实验项目 Test Items	参考标准 Reference	实验条件 Test Conditions	时间 Time	样品数 Quantity	判据 Criterion
冷热冲击 Thermal Shock	MIL-STD-202G	-40℃(15min)←→100℃(15min)	循环 200 次 200 cycles	22	0/22
湿热循环 Temperature And Humidity Cyclic	JEITA ED-4701 200 203	(-10~65)℃ , (0~90)%RH 24hrs./1cycle	循环 10 次 10 cycles	22	0/22
高温贮存 High Temperature Storage	JEITA ED-4701 200 201	Ta=100℃	1000h	22	0/22
低温贮存 Low Temperature Storage	JEITA ED-4701 200 202	Ta=-40℃	1000h	22	0/22
常温寿命试验 Lifespan Test	JESD22-A108D	Ta=25℃ If =10mA	1000h	22	0/22
耐焊接热 Resistance to Soldering Heat	GB/T 4937, II ,2.2&2.3	Tsol*=(260±5)℃ 10secs.	2 次 2 times	22	0/22

失效判断标准 Criteria For Judging Damage

测试项目 Test Items	符号 Symbol	测试条件 Test Conditions	判定标准 Criteria For Judging Damage
正向电压 Forward Voltage	V _F	I _F = I _{FT}	初始值±10% Initial Data±10%
反向电流 Reverse Current	I _R	V _R = 5V	I _R ≤10μA
光强 Luminous Intensity	I _V	I _F = I _{FT}	I _V 衰减≤50% IV degradation≤50%
耐焊接热 Resistance to Soldering Heat			无死灯 no dead light


* 注: Tsol-锡液温度; I_{FT}: 典型电流

* Note: Tsol-Temperature of tin liquid; I_{FT}: Typical current.

包装 (1)

Packaging (1)


✧ 载带 Carrier Tape



单位: mm, 未注公差: ± 0.1 mm
All dimensions in mm, tolerances unless mentioned is ± 0.1 mm.

✧ 编带细节 Details Of Carrier Tape


前进方向 Progressive Direction →



A: 盖带, 200 mm; B: 引导, 空带, 200mm; C: 编载产品 5000 只; D: 尾部, 空带, 200mm
A: Top Cover Tape, 200mm; B: Leader, Empty, 200mm; C: 5000 Lamps Loaded; D: Trailer, Empty, 200mm.

✧ 带盘 Reel Dimension


前进方向 Progressive Direction →




包装 (2)

Packaging(2)

✧ 防潮抗静电包装 Moisture Proof and Anti-Electrostatic Foil Bag



✧ 外包装箱 Cardboard Box



✧ 标签说明 Label Explanation

TYPE: 产品型号

QTY: 数量 Quantity

SC: 分档编号 Step Code

BIN: 档次 Rank

LOT: 批号 Lot Number

λ_d : 波长范围 Wavelength Range

IV: 光强范围 Luminous Intensity Range

VF: 正向电压范围 Forward Voltage Range

IF: 测试电流 Testing Current

	CHIP LED	
TYPE: XX-XXXXX-XX		XXXXX
QTY: XXXX	SC: XXX	
LOT: XXXXX	BIN: XXX	
IF(mA)	IV(mcd)	λ_d (nm)
VF(V)		
QC:		
XX: (XX) (XXX-XXX) (XXX-XXX) (XX-XX)		
XX: (XX) (XXX-XXX) (XXX-XXX) (XX-XX)		
FOSHAN NATIONSTAR OPTOELECTRONICS CO., LTD		
佛山市国星光电股份有限公司		