

HT75XX Series

27V 100mA Positive voltage regulators

WWW.TECHPUBLIC.COM


Features

- 4 μ A Current at no Load
- $\pm 2\%$ Output Accuracy
- 100mA Output Current
- Current Limit Protection

Applications

- Industrial Controls
- Home Automation
- Modules (Wireless, Camera, etc.)
- Portable, Battery Powered Equipment

PIN CONFIGURATION



Pin Number	Pin Name	Pin Function
SOT23-5		
1	VIN	Input of Supply Voltage
2	GND	Ground
3	EN	Enable Control Input
4	NC	No Internal Connection
5	VOUT	Output of the Regulator

Ordering Information

HT75XX-7

PACKAGE TYPE
7: SOT23-5

OUTPUT VOLTAGE

- 25: 2.5V
- 28: 2.8V
- 30 : 3.0V
- 33 : 3.3V
- 36 : 3.6V
- 44 : 4.4V

Example: HT7533-7
→ 3.3V Version, in SOT23-5 Package
& Tape & Reel Packing Type

HT75XX Series

27V 100mA Positive voltage regulators


WWW.TECHPUBLIC.COM

Absolute Maximum Ratings


over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
VIN	Continuous input voltage range	-0.3	28	V
VOUT	Output voltage range	-0.3	6	
EN	EN pin voltage range	-0.3	28	
IOUT	Output pin current	Internally limited		mA
Temperature	Operating Temperature Range ,Topr	-40	+85	°C
	Storage, Tstg	-40	+125	

BLOCK DIAGRAM



Typical Application Circuit



HT75XX Series

27V 100mA Positive voltage regulators

WWW.TECHPUBLIC.COM

Electrical Characteristics

(VIN=15V, VEN=5V, TA=25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST Conditions	MIN	TYP	MAX	UNIT
Supply Voltage	VIN		2	--	27	V
Output current	IOUT		150	--	--	mA
DC Output Voltage Accuracy		IOUT = 1mA	-2	--	2	%
Dropout Voltage (VIN-VOUT)	IOUT = 100mA	VOUT = 3.0V	--	450	--	mV
		VOUT = 3.3V	--	420	--	
		VOUT = 3.6V	--	400	--	
		VOUT = 5.0V	--	350	--	
Ground Current (IOUT = 0mA)	IQ	VOUT = 3.3V	--	--	4	uA
Shutdown Ground Current	ISD	VEN = 0V,	--	0.01	1	
VOUT Shutdown Leakage Current	ILEAK	VOUT = 0V	--	0.01	1	
Enable Threshold Voltage	VIH	EN Rising	1.1	--	--	V
	VIL	EN Falling	--	--	0.4	
EN Input Current	IEN	VEN = 5V	--	10	100	nA
Line Regulation	ΔLINE	IOUT = 1mA, 2 ≤ VIN ≤ 5V	--	0.3	--	%
Load Regulation	ΔLOAD	10mA ≤ IOUT ≤ 100mA	--	0.3	--	
Output Current Limit	ILIM	VOUT = 0.9 × VOUT(NOM)	200	--	--	mA
Power Supply Rejection Ratio	PSRR	VOUT = 3.3V, IOUT = 40mA, VIN = 5.5V, f = 1kHz	--	70	--	dB
Package Thermal Resistance θJA (Note 1)	Thermal Resistance Junction-to-Ambient		--	210	--	°C/W
Total Power Dissipation TC=25°C	PDTOT		--	0.2	--	W

Note: Test condition: For SOT23-5, the device is mounted on FR-4 substrate PC board, with minimum recommended pad layout.







HT75XX Series

27V 100mA Positive voltage regulators

WWW.TEHPUBLIC.COM


Typical Operating Characteristics (25 °C, unless otherwise noted)

Unless otherwise specified: $T_A = 25^\circ\text{C}$, $V_{IN} = V_O(\text{NOM}) + 1\text{ V}$, $C_{OUT} = 1\ \mu\text{F}$, $C_{IN} = 1\ \mu\text{F}$ all voltage options, EN pin tied to V_{IN} .



Package Outline Dimensions (unit: mm)

SOT23-5



Mounting Pad Layout (unit: mm)

