







RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



(Tolerance: ± 0.1)
(P.C.B thickness $t=1.0, 1.2$)



重点管控序号①-⑩尺寸

7	Pan slice	Ag-plating/ Stainless steel
6	Brush	C5210
5	Spring	SUS301
4	Support	C6191/Ag-plating
3	Mould	PA46
2	Signal body	CE191/PA46/Ag- Plating
1	Shaft	PA46
ITEM	Name	MATERIAL

Mechanical

Actuation Force	Operating Force(gf)
YTS23-E0035-A2B	400gf

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO., LTD.
Email at info@yiyuanswitches.com

L ≤ 10	± 0.30	UNITS mm	深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD
10 < L ≤ 30	± 0.50		
30 < L ≤ 100	± 1.0	MAT'L	Series NO. YTS23-E0035-A2B
角度	± 5°		
FINISH		Q'TY	TITLE: 卧式SMT内贴型, 7.8*3.8编码器, 安装高度6.5, 轴径3.0
APPD: ROGER		CHKD: ROC	DWG NO.: YTS23-E0035-A2B
DR: BILLY WANG 2020/08/21			SCALE SHEET REV. 1/1 1/1 A1