




DO - 27

Features

- ✧ Low power loss, high efficiency.
- ✧ High current capability, Low VF.
- ✧ High reliability
- ✧ High surge current capability.
- ✧ Epitaxial construction.
- ✧ Guard-ring for transient protection.
- ✧ For use in low voltage, high frequency inverter, free wheeling, and polarity protection application

Mechanical Data

- ✧ Cases: DO-27, Molded plastic
- ✧ Polarity: Color band denotes cathode
- ✧ High temperature soldering guaranteed: 260°C/10 seconds/.375", (9.5mm) lead lengths at 5 lbs., (2.3kg) tension
- ✧ Weight: 1.2 grams



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	SR 820	SR 830	SR 840	SR 850	SR 860	SR 890	SR 8100	SR 8200	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	20	30	40	50	60	90	100	200	V
Maximum RMS Voltage	V _{RMS}	14	21	28	35	42	63	70	140	V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	50	60	90	100	200	V
Maximum Average Forward Rectified Current See Fig. 1	I _(AV)	5.0								A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	120								A
Maximum Instantaneous Forward Voltage @5.0A	V _F	0.55			0.70		0.85			V
Maximum D.C. Reverse Current @ T _A =25 °C at Rated DC Blocking Voltage @ T _A =125 °C	I _R	0.5					0.1			mA mA
		15			10		5.0		1.0	
Typical Junction Capacitance (Note 2)	C _j	250			210		120			pF
Typical Thermal Resistance (Note 1)	R _{θJA}	35					10			°C/W
	R _{θJC}	2					2			
Operating Junction Temperature Range	T _J	-65 to +150								°C
Storage Temperature Range	T _{STG}	-65 to +150								°C

- Notes:
1. Mount on Cu-Pad Size 5mm x 5mm on P.C.B.
 2. Measured at 1 MHz and Applied Reverse Voltage of 4.0V D.C.

Ratings AND Characteristic Curves

FIG.1 -- FORWARD CURRENT DERATING CURVE




FIG.2 -- PEAK FORWARD SURGE CURRENT




FIG.3 -- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS

