


## SiC Schottky Diodes

### FEATURES

- ◆ Reverse withstand voltage 650V
- ◆ Zero reverse recovery current
- ◆ High working frequency
- ◆ Switch characteristics are not affected by temperature
- ◆ Fast switching speed
- ◆ Positive temperature coefficient of positive pressure drop



### Application

- ◆ Switching mode power supply, AC/DC converter
- ◆ Power factor correction
- ◆ Motor drive
- ◆ PV inverter and wind turbine

### Advantages

- ◆ Very low switching loss
- ◆ Higher efficiency
- ◆ Low dependence of the system on the heat sink
- ◆ No thermal collapse in parallel devices

### Absolute Maximum Rating (Per Leg, Ta=25°C)





Parameter	Symbol	Test conditions	Value	Unit
Peak repetitive reverse voltage	V <sub>RRM</sub>		650	V
Working Peak Reverse voltage	V <sub>RWM</sub>		650	V
DC Blocking Voltage	V <sub>DC</sub>		650	V
Continuous Forward Current	I <sub>F(AV)</sub>	T <sub>a</sub> =25°C T <sub>a</sub> =125°C T <sub>a</sub> =150°C	30 15 10	A
Repetitive Peak Forward Surge Current	I <sub>FRM</sub>	T <sub>c</sub> =25°C, tp=10ms, Half Sine Wave T <sub>c</sub> =110°C, tp=10ms, Half Sine Wave	46 31	A
Non-Repetitive Peak Forward Surge Current	I <sub>FSM</sub>	T <sub>c</sub> =25°C, tp=10ms, Half Sine Wave T <sub>c</sub> =110°C, tp=10ms, Half Sine Wave	90 71	A
Power dissipation	P <sub>tot</sub>	T <sub>a</sub> =25°C T <sub>a</sub> =110°C	115 50	W
Junction temperature	T <sub>j</sub>		-55 ~ +175	°C
Storage temperature	T <sub>stg</sub>		-55 ~ +175	°C
Mounting Torque	T <sub>M</sub>	M3 Screw 6-32 Screw	1 8.8	Nm lbf-in

### Thermal characteristics (Per Device)


Parameter	Symbol	Value	Unit
Thermal Resistance - Junction to Case	R <sub>θJC</sub>	0.75	°C/W

**Electrical Characteristics (Per Leg, Ta=25°C unless otherwise specified)**


Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Forward voltage	$V_F$	$I_F = 10A, T_j=25^\circ C$ $I_F = 10A, T_j=175^\circ C$		1.4 1.7	1.8 2.4	V
Reverse current	$I_R$	$V_R = 650V, T_j=25^\circ C$ $V_R = 650V, T_j=175^\circ C$		10 20	60 200	$\mu A$
Total capacitive charge	$Q_C$	$V_R = 650V, I_F = 10 A$ $dI/dt=500A/\mu s, T_j=25^\circ C$		30		nC
Total capacitance	C	$V_R = 0V, T_j=25^\circ C, f=1MHz$ $V_R = 200V, T_j=25^\circ C, f=1MHz$ $V_R = 400V, T_j=25^\circ C, f=1MHz$		460 50 48		pF
Capacitance Stored Energy	$E_C$	$V_R = 400V$		4.9		$\mu J$

**Typical Characteristics (Per Leg)**

**Figure 1. Forward Characteristics**

**Figure 2. Reverse Characteristics**

**Figure 3. Load current**

**Figure 4. Dissipated power curve**


**Typical Characteristics (Per Leg)**




**Figure 5. Capacitance vs reverse voltage**



**Figure 6. Capacitance vs. reverse voltage**



**Figure 7. Capacitance stored energy**



**Figure 8. Transient Thermal Impedance**

**Package Dimensions**

**TO-247**

Symbol	Dimensions in mm		Dimensions in Inch	
	Min.	Max.	Min.	Max.
A	4.90	5.10	0.193	0.201
A1	1.90	2.10	0.075	0.083
A2	2.29	2.54	0.090	0.100
b	1.00	1.40	0.039	0.055
b1	2.00	2.20	0.079	0.087
b2	3.00	3.20	0.118	0.126
c	0.50	0.70	0.020	0.028
D	15.75	16.05	0.620	0.632
E	20.20	20.80	0.795	0.819
e	5.45 (BSC)		0.215 (BSC)	
e1	10.90 (BSC)		0.429 (BSC)	
F	6.05	6.25	0.238	0.246
F1	5.80	6.00	0.228	0.236
L	20.10	20.40	0.791	0.803
L1	4.05	4.35	0.159	0.171
Φ	3.50	3.70	0.138	0.146

**ORDERING INFORMATION**

Part Number	Package	Marking	Pack
YFWD320065PT	TO-247	YFW D320065PT X X X X X	600pcs/box