




PART NO.	Packing reel	QTY
20279-001E-01	Corrugated paper reel	2500
20279-001E-02	Plastic reel	2500
20279-001E-03	Plastic reel	5000



RECOMMENDED FOOTPRINT PATTERN



Notes.

1. Material
 - (1) Housing : LCP, UL94V-0, white
 - (2) Contact : brass
 - Au 0.1 μ m MIN. over Ni 1.27 μ m MIN.
 - (3) Ground Contact : phosphor bronze
 - Au 0.05 μ m MIN. over Ni 1.27 μ m MIN.
 2. Coplanarity : 0.1mm MAX.
 3. Packing : emboss tape
 4. Mating partner Part No. :
 - 20278-***R-***
 - 20351-***R-***
 - 20311-***R-***
5. This is "Pb-free" connector.
6. RoHS compliant. DC0-7.2GHz


Notes.

1. 材料
 - (1) ハウジング : LCP, UL94V-0, 白色
 - (2) コタテ : 黄銅
 - 金メッキ 0.1 μ m MIN. 下地 ニッケルメッキ 1.27 μ m MIN.
 - (3) グラウンドコタテ : リン青銅
 - 金メッキ 0.05 μ m MIN. 下地 ニッケルメッキ 1.27 μ m MIN.
 2. コプラナリティ : 0.1mm MAX.
 3. 梱包 : エンボステープ
 4. 嵌合相手 Part No. :
 - 20278-***R-***
 - 20351-***R-***
 - 20311-***R-***
5. 本コネクタは "Pb-free" である
6. RoHS指令を満足している


MATING

Plug P/N 20278-***R-***
20351-***R-37

4 ± 0.4 at 20278-***R-08, 13, 32
4.7 ± 0.4 at 20278-***R-18
4.7 ± 0.4 at 20351-***R-37



Plug P/N 20311-***R-***



GENERAL TOLERANCE	
6 MAX.	± 0.2
6 OVER MAX. 30	± 0.3
30 OVER MAX. 120	± 0.5
ANGLE	$\pm 2^\circ$

14	Z12046 H.M	50n / 20 / 12	FK	DESIGN BY	K.Obayashi	Jun./07/01	DATE
13	Z10262 H.M	Jun./08/11	E.K	CHKD BY			DATE
12	Z11032 Y.H	Jan./28/11	E.K				
11	Z11030 H.M	Jan./26/11	E.K				
10	Z10101 Y.H	Mar./08/10	E.K	APPD BY	E.Kawabe	Jun./07/01	DATE
REV	ECN	BY	DATE	APP			
REV/RECORD				CUSTOMER	K.Katabuchi	Jun./07/01	DATE
SERIES No.				COPY			
R7							
PROJECTION				SCALE	UNIT	DWG. No.	SHEET
10:1				mm		20279	1/1
							REV.
							14

I-PEX DAICHI SEIKO CO.,LTD.
I-Pex Business Company

TITLE
MHF series micro coaxial
connector receptacle vertical