










Product NO.		DOSIN-801-0341		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	First issue	Mr. Wang	16/01/28	John kine



Specification:

Impedance: 75 Ohms

VSWR:1.3MAX

Frequency range:DC~3G

Working Voltage:500V rms @ sea level

Insulation resistance:5000 Ohms min

Temperature range:-65°C TO +165°C

Relative temperature:≤95%(40° C±2° C)

Drawings products are in line with ROHS standards.

PCB MOUNTING HOLE

1	Body	Zinc	NI:80-120u"	NOTE:	Tolerance	X.	±0.15	 Dosin Industrial(H.K)Co.Ltd E-mail:dosin2005@163.com dosin2005@dosin-china.com 东莞市德索五金电子制品有限公司 Web:http://www.china-guan.com Dosin Hardware Electronics Co.,Ltd TEL:(0086)769-81153906 FAX:(0086)769-81875836					
2	Center contact	Brass	AU:1u"			X. X	±0.10						
3	Insulator	PTFE	White			X. XX	±0.05						
4	Washer	IRON	NI:80-120u"			Angular	±5°						
5	Hex nut	Brass	NI:80-120u"										
6				DRAWN	View		Name: BNC JACK CONNECTOR						
7				Zelin. Zhang									
8				CHECKED									
9													
10				APPROVALS									
NO	Component Number	Material	Finish		SCALE	1:1	DateTime 2016.01.28	CAD FILE D/company drawings/BD	SHEET: 1 OF 1				
A		B		C		D		E		F		G	