

## ■ Features

- Assemblage design, sturdy structure.
- High inductance, high current, low magnetic loss, low ESR, small parasitic capacitance.
- Flat wire winding, achieve a low D.C. Resistance.
- Temperature rise current and saturation current is less influenced by environment.
- Operating temperature range:  $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$ .

## ■ Applications

- Low profile, high current power supplies.
- Battery powered devices.
- DC/DC converters in distributed power systems.
- DC/DC converters for field programmable gate array.

## ■ Product Identification

$\frac{\text{YSFP}}{(1)} \quad \frac{\square\square\square\square\square}{(2)} - \frac{\square\square\square}{(3)} \quad \frac{\square}{(4)}$


(1) : Type

(2) : Dimensions

(3) : Inductance value

(4) : Inductance Tolerance: M= $\pm 20\%$ , K= $\pm 10\%$ , J= $\pm 5\%$

## ■ Shapes and Dimensions (Unit: mm)



TYPE	A Max.	B Max.	C Max.	D Max.	E	F	G
YSFP2920S	28.0	19.7	21.0	28.5	4.0 $\pm$ 0.5	10.0 $\pm$ 1.0	4.5 $\pm$ 0.5

## ■ Electrical requirements

Part Number	L (uH)	Test Freq.	DCR Max.(mΩ)	I sat (A)	I rms (A)
YSFP2920S-330M	33±20%	100KHz/0.25V	2.5	11	33

※ All test data is based on 25 °C ambient.


※ DC current(A) that will cause an approximate  $\Delta T 40^{\circ}\text{C}$ .

※ DC current(A) that will cause L0 to drop approximately 30% Typ.


※ The part temperature (ambient + temp rise) should not exceed  $125^{\circ}\text{C}$  under worst case operating conditions.

Circuit design, component, PWB trace size and thickness, airflow and other cooling provision all affect the part temperature. Part temperature should be verified in the den application.


## ■ Electrical schematics



## ■ Recommended PCB Layout




■ Saturation current VS temperature rise current curve



## ■ Reliability

Item	Specification and Requirement	Test Method
Solder ability test	Terminals area must have 95% min solder coverage	Solder heat proof: ① Preheating: $160 \pm 10^{\circ}\text{C}$ for 90 seconds ② Retention time: $245 \pm 5^{\circ}\text{C}$ for $2 \pm 0.5$ seconds
Vibration test	Inductance change: Within $\pm 5\%$ Without Mechanical damage such as break	① Vibration frequency: (10Hz to 55Hz to 10Hz) in 60 seconds as a period ② Vibration time: Period cycled for 2 hours in each of 3 mutual perpendicular directions. ③ Amplitude: 1.5mm Max.
Shock test	Inductance change: Within $\pm 5\%$ Without Mechanical damage such as break	① Peak value: 100G. ② Duration of pulse: 11ms. ③ Times in each positive and negative direction of 3 mutual perpendicular directions
Thermal shock	Inductance change: Within $\pm 5\%$ Without Mechanical damage such as break	① Repeat 100 cycle as follow ( $-55 \pm 2^{\circ}\text{C}$ 30 $\pm$ 3 minutes), Room temperature, 5 minutes ( $+125 \pm 2^{\circ}\text{C}$ , 30 $\pm$ 3 minutes) ② Recovery: 48 $\pm$ 4/-0 hours of recovery Under the standard condition after the test. (see Note 1)
High temperature life test	Inductance change: Within $\pm 5\%$ Without Mechanical damage such as break	① Environment condition: $85 \pm 2^{\circ}\text{C}$ Applied current: Rated current ② Duration: 1000 $\pm$ 4/-0 hours (see Note 1)
Humidity Resistance	Inductance change: Within $\pm 5\%$ Without Mechanical damage such as break	① Environment condition: $60 \pm 2^{\circ}\text{C}$ Humidity: 90-95% Applied current: Rated current ② Duration: 1000 $\pm$ 4/-0 hours (see Note 1)
Low temperature life test	Inductance change: Within $\pm 5\%$ Without Mechanical damage such as break	Store temperature $-55 \pm 2^{\circ}\text{C}$ for total 1000 $\pm$ 4/-0 hours
High temperature life test	Inductance change: Within $\pm 5\%$ Without Mechanical damage such as break	Store temperature $+125 \pm 2^{\circ}\text{C}$ for total 1000 $\pm$ 4/-0 hours

## ■ Reflow Profile




## ■ Reflow Soldering Method

Reflow Soldering	Tp: 255 ~ 260°C Max. 30 seconds(tp)	
	217°C	60 ~ 150 seconds
Pre-Heat	150 ~ 200°C	60 ~ 150 seconds
Time 25°C to peak temperature	8 minutes Max.	

## ■ Soldering iron method

350±5°C Max. 3 seconds.

## ■ Packaging



Product Series	Quantity/Tray	Quantity/Carton
YSFP2920S	40 PCS	280 PCS