







02P



08P




8P and 8P following no reinforcement.



未注公差 (General tolerances)(mm)														D 0.1/10 ±2°
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	
~	~	~	~	~	~	~	~	~	~	~	~	~	~	
3	6	10	18	30	50	80	120	180	250	315	400	500		
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	
Z														±2°

PCB LAYOUT



2	Pin	Copper alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES
UL 标准:	UL Standard:	B	C D
额定电压/电流/ Rated Voltage/Current(A)	150/4	/	/
IEC 标准/ IEC Standard:			
过压类别/Overvoltage Category/污染等级/ Pollution Degree	III/3	III/2	II/2
额定电压/电流/ Rated Voltage(V)/Current(A)	/	/	250/5
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	/	/	2.5
间距/ Pitch(mm) 线数范围/ Poles	2.50/N=02~12P		
使用温度范围/ Operating temperature(°C)	-40~+105		
符合RoHS环保要求/ Conform to RoHS	Yes		

MATERIAL:

SURFACE:

MAT NO.: _____/

STATUS: /

APPD: | an CHH 2020.03.19

CHKD: Yu JZh 2020.03.19

DRAFT: LIN 2008.10.20

mm
(inch)

SIZE: A4

宁波高松电子有限公司


DEGSON®
 宁波高松电子有限公司
 NINGBO DEGSON ELECTRICAL CO., LTD

NAME: _____

15EDGVC-2.5-XXP-1Y-00A(H)

DRAWING NO.: 15EDGVC-2.5-C01

TYPE: CUSTOMER DRAWING

SCALE:2.5:1 SHEET 1/1

心理 中专 管发 文研

2020.03.19

(仅限内部使用,对外无效)