





SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

技术要求:

1. 塑件材料: PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 20m\Omega$
4. 绝缘电阻: $\geq 1000M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 3.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求。



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
A396E1L1-2Y2P11	2	3.96	7.92
A396E1L1-2Y3P11	3	7.92	11.88
A396E1L1-2Y4P11	4	11.88	15.84
A396E1L1-2Y5P11	5	15.84	19.80
A396E1L1-2Y6P11	6	19.80	23.76
A396E1L1-2Y7P11	7	23.76	27.72
A396E1L1-2Y8P11	8	27.72	31.68
A396E1L1-2Y9P11	9	31.68	35.64
A396E1L1-2Y10P11	10	35.64	39.60
...	...	...	...
A396E1L1-2Y20P11	20	$(20-1)\times 3.96$	$(20+1)\times 3.96$

2	端子 Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍 30u"MIN, 再镀锡80u"MIN
1	基座 Wafer	LCP (UL94V-0)	1	米色
序号	名称	材料	数量	备注

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.20	X.* ±10°	PART NO. A396E1L1-2YXP11		TITLE: VH3.96MM 直针 带扣	
.XX ±0.10	.X.* ± 8°				
.XXX ±0.05	.XX.* ± 5°				
UNITS	mm	DESIGN: Ethan		MANUFACTURE DWG 	
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE	SHEET
				N:A	1/1