

General Description

The CMSA070N10 uses advanced SGT technology to provide excellent RDS(ON). It can be used in a wide variety of applications.

Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant


Product Summary

BVDSS	RDS(on) max.	ID
100V	7mΩ	90A

Applications

- DC/DC Converter
- Primary Side Switch

DFN-8 5x6 Pin Configuration



Type	Package	Marking
CMSA070N10	DFN-8 5x6	CMSA070N10

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	100	V
V_{GS}	Gate-Source Voltage	±20	V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current	90	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current	63	A
I_{DM}	Pulsed Drain Current	360	A
EAS	Single Pulse Avalanche Energy ¹	162	mJ
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation	115	W
T_{STG}	Storage Temperature Range	-55 to 150	°C
T_J	Operating Junction Temperature Range	150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient(min. footprint)	---	50	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-case	---	1.12	°C/W

Electrical Characteristics($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	100	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=28A$	---	6.2	7	mΩ
		$V_{GS}=4.5V$, $I_D=25A$	---	8.1	9.5	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1.0	---	3.0	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=100V$, $V_{GS}=0V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	28	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	1.0	---	Ω
Q_g	Total Gate Charge	$I_D=30A$	---	41	---	nC
Q_{gs}	Gate-Source Charge	$V_{DD}=50V$	---	10.3	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$	---	7.5	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=50V$ $V_{GS}=10V$ $R_{G_ext}=2.7\Omega$	---	11	---	ns
T_r	Rise Time		---	36	---	
$T_{d(off)}$	Turn-Off Delay Time		---	33	---	
T_f	Fall Time		---	10.3	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2050	---	pF
C_{oss}	Output Capacitance		---	1050	---	
C_{rss}	Reverse Transfer Capacitance		---	60	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	90	A
I_{SM}	Pulsed Source Current		---	---	360	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=25A$, $T_J=25^{\circ}\text{C}$	---	0.85	1.4	V

Note :







1. The EAS data shows Max. rating . The test condition is $V_{DD}=50V$, $V_{GS}=10V$, $L=1\text{mH}$, $I_{AS}=18A$.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design, functions and reliability without notice.


Typical Characteristics



Package Dimension

DFN-8 5x6

Unit :mm



注:

1. 未注公差 ± 0.05 未标注圆角 $R_{\max} = 0.25$

Dimensions In Millimeters			
Symbol	Min.	Max.	Ave.
A	0.900	1.100	1.000
D	4.950	5.150	5.050
D1	3.850	4.250	4.050
E	5.750	5.950	5.850
E1	5.950	6.350	6.150
E2	3.300	3.700	3.500
E3	0.900	1.300	1.100
b	0.250	0.350	0.300
e	1.220	1.320	1.270
L	0.585	0.785	0.685
L1	0.525	0.725	0.625
Ø	1.000	1.400	1.200
L2	0~0.100		
L3	0~0.100		