








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN


NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
D200F2W1-2W2P43	2	2.00	8.00	6.80
D200F2W1-2W3P43	3	4.00	10.00	8.80
D200F2W1-2W4P43	4	6.00	12.00	10.80
D200F2W1-2W5P43	5	8.00	14.00	12.80
D200F2W1-2W6P43	6	10.00	16.00	14.80
D200F2W1-2W7P43	7	12.00	18.00	16.80
D200F2W1-2W8P43	8	14.00	20.00	18.80
D200F2W1-2W9P43	9	16.00	22.00	20.80
D200F2W1-2W10P43	10	18.00	24.00	22.80
D200F2W1-2W11P43	11	20.00	26.00	24.80
D200F2W1-2W12P43	12	22.00	28.00	26.80
D200F2W1-2W13P43	13	24.00	30.00	28.80
D200F2W1-2W14P43	14	26.00	32.00	30.80
D200F2W1-2W15P43	15	28.00	34.00	32.80
D200F2W1-2W16P43	16	30.00	36.00	34.80

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. D200F2W1-2WXP43	TITLE: WAFER 2.00 贴片		
.XX ±0.20	X.X° ±3°		MANUFACTURE DWG		
.XXX ±0.10	X.XX° ±1°				
UNITS	mm	DESIGN: Ethan	 SCALE N:A SHEET 1/1		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			