

# CMD60R290Q/CMU60R290Q

600V, 0.27Ω typ., 13.8A N-Channel Super Junction Power MOSFET

## General Description

The 60R290Q is power MOSFET using CMOS's advanced super junction technology that can realize very low on resistance and gate charge. It will provide much high efficiency by using optimized charge coupling technology. These user friendly devices give an advantage of Low EMI to designers as well as low switching loss.

## Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant


## Product Summary

| BVDSS | R <sub>DS(on)</sub> max. | ID    |
|-------|--------------------------|-------|
| 600V  | 300mΩ                    | 13.8A |

## Applications

- Adapter
- PFC Power Supply Stages
- Switching Applications

## TO-252/251 Pin Configuration



## Absolute Maximum Ratings

| Symbol                                | Parameter                                  | Rating     | Units |
|---------------------------------------|--------------------------------------------|------------|-------|
| V <sub>DS</sub>                       | Drain-Source Voltage                       | 600        | V     |
| V <sub>GS</sub>                       | Gate-Source Voltage                        | ±30        | V     |
| I <sub>D</sub> @T <sub>C</sub> =25°C  | Continuous Drain Current                   | 13.8       | A     |
| I <sub>D</sub> @T <sub>C</sub> =100°C | Continuous Drain Current                   | 8.7        | A     |
| I <sub>DM</sub>                       | Pulsed Drain Current                       | 55.2       | A     |
| EAS                                   | Single Pulse Avalanche Energy <sup>1</sup> | 375        | mJ    |
| P <sub>D</sub> @T <sub>C</sub> =25°C  | Total Power Dissipation                    | 85         | W     |
| T <sub>STG</sub>                      | Storage Temperature Range                  | -55 to 150 | °C    |
| T <sub>J</sub>                        | Operating Junction Temperature Range       | 150        | °C    |

## Thermal Data

| Symbol           | Parameter                           | Typ. | Max. | Unit |
|------------------|-------------------------------------|------|------|------|
| R <sub>θJA</sub> | Thermal Resistance Junction-ambient | ---  | 62.5 | °C/W |
| R <sub>θJC</sub> | Thermal Resistance Junction-case    | ---  | 1.47 | °C/W |

# CMD60R290Q/CMU60R290Q

600V, 0.27Ω typ., 13.8A N-Channel Super Junction Power MOSFET

## Electrical Characteristics(T<sub>J</sub>=25°C, unless otherwise noted)

| Symbol              | Parameter                         | Conditions                                               | Min. | Typ. | Max. | Unit |
|---------------------|-----------------------------------|----------------------------------------------------------|------|------|------|------|
| BV <sub>DSS</sub>   | Drain-Source Breakdown Voltage    | V <sub>GS</sub> =0V, I <sub>D</sub> =250uA               | 600  | ---  | ---  | V    |
| R <sub>DS(ON)</sub> | Static Drain-Source On-Resistance | V <sub>GS</sub> =10V, I <sub>D</sub> =6.5A               | ---  | 270  | 300  | mΩ   |
| V <sub>GS(th)</sub> | Gate Threshold Voltage            | V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =250uA | 2    | ---  | 4    | V    |
| I <sub>DSS</sub>    | Drain-Source Leakage Current      | V <sub>DS</sub> =600V, V <sub>GS</sub> =0V               | ---  | ---  | 1    | μA   |
| I <sub>GSS</sub>    | Gate-Source Leakage Current       | V <sub>GS</sub> =±30V, V <sub>DS</sub> =0V               | ---  | ---  | ±100 | nA   |
| g <sub>fs</sub>     | Forward Transconductance          | V <sub>DS</sub> =10V, I <sub>D</sub> =6.5A               | ---  | 10.5 | ---  | S    |
| R <sub>g</sub>      | Gate Resistance                   | V <sub>DS</sub> =0V, V <sub>GS</sub> =0V, f=1MHz         | ---  | 7    | ---  | Ω    |
| Q <sub>g</sub>      | Total Gate Charge                 | I <sub>D</sub> =13.8A                                    | ---  | 31   | ---  | nC   |
| Q <sub>gs</sub>     | Gate-Source Charge                | V <sub>DS</sub> =480V                                    | ---  | 8    | ---  |      |
| Q <sub>gd</sub>     | Gate-Drain Charge                 | V <sub>GS</sub> =10V                                     | ---  | 11   | ---  |      |
| T <sub>d(on)</sub>  | Turn-On Delay Time                | V <sub>DS</sub> =300V                                    | ---  | 20   | ---  | ns   |
| T <sub>r</sub>      | Rise Time                         | V <sub>GS</sub> =10V                                     | ---  | 43   | ---  |      |
| T <sub>d(off)</sub> | Turn-Off Delay Time               | R <sub>G</sub> =25Ω                                      | ---  | 91   | ---  |      |
| T <sub>f</sub>      | Fall Time                         | I <sub>D</sub> =13.8A                                    | ---  | 42   | ---  |      |
| C <sub>iss</sub>    | Input Capacitance                 | V <sub>DS</sub> =45V, V <sub>GS</sub> =0V, f=1MHz        | ---  | 940  | ---  | pF   |
| C <sub>oss</sub>    | Output Capacitance                |                                                          | ---  | 580  | ---  |      |
| C <sub>rss</sub>    | Reverse Transfer Capacitance      |                                                          | ---  | 10   | ---  |      |

## Diode Characteristics

| Symbol          | Parameter                 | Conditions                                        | Min. | Typ. | Max. | Unit |
|-----------------|---------------------------|---------------------------------------------------|------|------|------|------|
| I <sub>S</sub>  | Continuous Source Current | V <sub>G</sub> =V <sub>D</sub> =0V, Force Current | ---  | ---  | 13.8 | A    |
| I <sub>SM</sub> | Pulsed Source Current     |                                                   | ---  | ---  | 55.2 | A    |
| V <sub>SD</sub> | Diode Forward Voltage     | V <sub>GS</sub> =0V, I <sub>S</sub> =12A          | ---  | 0.87 | 1.4  | V    |
| t <sub>rr</sub> | Reverse Recovery Time     | V <sub>DD</sub> =100V, I <sub>S</sub> =13.8A      | ---  | 364  | ---  | ns   |
| Q <sub>rr</sub> | Reverse Recovery Charge   | di/dt=100A/μs                                     | ---  | 4.7  | ---  | μC   |

Note :







1.The EAS data shows Max. rating . The test condition is V<sub>DD</sub>=100V, V<sub>GS</sub>=10V, L=30mH, I<sub>AS</sub>=5A.

This product has been designed and qualified for the counsumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserver the right to improve product design ,functions and reliability wihtout notice.


### Typical Characteristics



## Package Dimension

TO-252

Unit :mm



# CMD60R290Q/CMU60R290Q

600V, 0.27Ω typ., 13.8A N-Channel Super Junction Power MOSFET

## Package Dimension

TO-251A

Unit :mm

