

CMP035N10/CMB035N10/CMI035N10/CMF035N10

100V, 2.9mΩ typ., 180A N-Channel MOSFET

General Description

The 035N10 uses advanced SGT technology to provide excellent RDS(ON). This device is well suited for high efficiency fast switching applications.

Product Summary

BVDSS	R _{DS(on)} max.	ID
100V	3.5mΩ	180A


Applications

- Motor control and drive
- Battery management

Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant

TO-220/263/262/220F Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	220/263/262	220F	Units
V _{DS}	Drain-Source Voltage	100		V
V _{GS}	Gate-Source Voltage	±20		V
I _D @T _C =25°C	Continuous Drain Current	180	180*	A
I _D @T _C =100°C	Continuous Drain Current	126	126*	A
I _{DM}	Pulsed Drain Current	720	720*	A
EAS	Single Pulse Avalanche Energy (Note 1)	2722		mJ
P _D @T _C =25°C	Total Power Dissipation	300	45	W
T _{STG}	Storage Temperature Range	-55 to 150		°C
T _J	Operating Junction Temperature Range	-55 to 150		°C

* Drain current limited by maximum junction temperature.

Thermal Data

Symbol	Parameter	220/263/262	220F	Unit
R _{θJA}	Thermal Resistance Junction-ambient Max.(min. footprint)	62	62	°C/W
R _{θJC}	Thermal Resistance Junction-case Max.	0.42	2.78	°C/W

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	100	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=50A$	---	2.9	3.5	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	---	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=100V$, $V_{GS}=0V$	---	---	1	uA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=20A$	---	43	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2.0	---	Ω
Q_g	Total Gate Charge	$V_{DD}=50V$, $I_D=50A$ $V_{GS}=10V$	---	117	---	nC
Q_{gs}	Gate-Source Charge		---	40	---	
Q_{gd}	Gate-Drain Charge		---	37	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=50V$, $I_D=10A$ $R_G=3\Omega$	---	48	---	ns
T_r	Rise Time		---	56	---	
$T_{d(off)}$	Turn-Off Delay Time		---	75	---	
T_f	Fall Time		---	33	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	8000	---	pF
C_{oss}	Output Capacitance		---	2600	---	
C_{rss}	Reverse Transfer Capacitance		---	300	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Diode continuous forward current	$V_G=V_D=0V$, Force Current	---	---	180	A
$I_{S,pulse}$	Diode pulse current		---	---	720	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_F=50A$, $T_J=25^{\circ}\text{C}$	---	0.85	1.4	V

Note :







1.The EAS data shows Max. rating .The test condition is $V_{DS}=80V$, $V_{GS}=10V$, $L=5\text{mH}$, $I_{AS}=33A$.


This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.


Cmos reserves the right to improve product design ,functions and reliability without notice.

Typical Characteristics




Package Dimension
TO-220
Unit :mm



DIM	MILLIMETERS
A	10.0±0.3
A1	8.64±0.2
A2	1.15±0.1
A3	5.0±0.2
B	15.8±0.4
B1	13.2±0.3
C	4.56±0.1
C1	1.3±0.2
D	0.8±0.2
E	3.6±0.2
F	2.95±0.3
G	6.5±0.3
H	0.5±0.1
K	3.1±0.2
L	13.2±0.4
M	1.25±0.1
N	2.54±0.1
P	2.4±0.3
Q	9.0±0.3
T	W:0.35
DIA	⊙1.5 (deep 0.2)

Package Dimension
TO-263
Unit :mm


DIM	MILLIMETERS
A	9.8 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	15.5 ± 0.3
h	1.54 ± 0.2
h1	10.5 ± 0.2
h2	9.2 ± 0.1
h3	1.54 ± 0.2
h4	2.7 ± 0.2
L	2.4 ± 0.2
1	1.3 ± 0.1
11	0.8 ± 0.1
12	1.3 ± 0.1
13	0.5 ± 0.1
N	2.54 ± 0.1
R	$0.5R \pm 0.05$

Package Dimension
TO-262
Unit :mm


DIM	MILLIMETERS
A	9.98 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	23.9 ± 0.3
h	3.1 ± 0.2
h1	9.16 ± 0.2
h2	13.2 ± 0.2
L	0.5 ± 0.1
l1	1.3 ± 0.1
l2	0.8 ± 0.1
N	2.45 ± 0.1

Package Dimension
TO-220F
Unit :mm


DIM	MILLIMETERS
A	10.16±0.3
A1	7.00±0.1
A2	3.3±0.2
A3	9.5±0.2
B1	15.87±0.3
B2	4.7±0.2
B3	6.68±0.4
C	3.3±0.2
C1	12.57±0.3
C2	10.02±0.5
D	2.54±0.05
D1	1.28±0.2
D2	0.8±0.1
K	3.1±0.3
E1	2.54±0.1
E3	0.5±0.1
E4	2.76±0.2
DIA	⌀1.5 (deep 0.2)