


Remarks:

1. Do not cut off copper wire when cutting wire.
 2. Do not burn wire when baking heat-shrink tube.
 3. Pull-force of terminal should reach the standard.
 4. Hook/clasp the wire and solder with terminal of socket.

Test condition

1. Short/open circuit: 100% test

序号	名称	数量	规 格
1	AC插座	1	RT-C14-L00B-AA 10A/15A 250VAC
2	热缩套管	4	黑色热缩套管 L=15mm
3	线材	1	UL3385 18AWG 颜色: 黑色线
4	线材	1	UL3385 18AWG 颜色: 黄绿色地线
5	线材	1	UL3385 18AWG 颜色: 棕色线
6	线材	1	UL3385 18AWG 颜色: 蓝色线
7	圆环端子	1	$\varnothing 7.5 \times ID 4.0 \times T 0.4 \text{mm}$ 镀锡端子
8	快插端子	2	187 快插端子带透明套管
9	热缩套管	2	黑色热缩套管 L=20mm
10	胶壳	1	VH-3.96-5Y 白色胶壳
11	端子	2	VH-3.96 镀锡端子



焊接(钩焊)示意图		Wiring table	
插座焊接端子		N	黑色线
线材导体	线材	E	黄绿色地线
		L	棕色线

△5	→	△10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN MM		SCALE NO	MAT'L ***	MATERIAL NO.	DRAWING NO.	REV.	
				RANGE	TOLERANCE					X	±10			X.X	±5	X.XX	±5
△4	→	△9	→	△8	→	△7	→	△6	→	△1	→	NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°
△3	→	△10	→	△9	→	△8	→	△7	→	△6	→	△1	→	△10	→	△9	→
△2	→	△8	→	△7	→	△6	→	△5	→	△4	→	△3	→	△10	→	△9	→
△1	→	△7	→	△6	→	△5	→	△4	→	△3	→	△2	→	△10	→	△9	→
NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION

东莞市六钧电子五金有限公司

RT-C14-L00B-AA-43

***** AO