

MSKSEMI 美森科

SEMICONDUCTOR



ESD



TVS



TSS



MOV



GDT



PLED

2N7002DWH6327-MS

Product specification



General Features

- 60V,0.3A,RDS(ON)=1.8Ω@VGS=10V
Improved dv/dt capability
- Fast switching
- Green Device Available
- G-S ESD Protection Diode Embedded

Application

- Motor Drive
- Power Tools
- LED Lighting

Reference News

PACKAGE OUTLINE	Pin Configuration	Marking
		
SOT-363		

Absolute Maximum Ratings (TA=25°C unless otherwise

Symbol	Parameter	Rating	Units
V _{DS}	Drain- Source Voltage	60	V
V _{GS}	Gate- Source Voltage	±20	V
I _D	Drain Current – Continuous (T _A =25 °C)	0.3	A
	Drain Current – Continuous (T _A =70 °C)	0.24	A
I _{DM}	Drain Current – Pulsed ¹	1.2	A
P _D	Power Dissipation (T _A =25 °C)	0.28	W
	Power Dissipation – Derate above 25	0.002	W/°C
T _{STG}	Storage Temperature Range	-50 to 150	°C
T _J	Operating Junction Temperature Range	-50 to 150	°C

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction to ambient	---	450	°C/W

Electrical Characteristics(T_J=25 °C , unless otherwise noted)
Off Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
B _V D _{SS}	Drain- Source Breakdown Voltage	V _{GS} =0V , I _D =250uA	60	---	---	V
ΔB _V D _{SS} / ΔT _J	B _V D _{SS} Temperature Coefficient	Reference to 25 °C , I _D =1 mA	---	0.04	---	V/°C
I _{DSS}	Drain- Source Leakage Current	V _{DS} =60V , V _{GS} =0V , T _J =25	---	---	1u	A
		V _{DS} =48V , V _{GS} =0V , T _J =125	---	---	100u	A
I _{GSS}	Gate- Source Leakage Current	V _{GS} = ±20V , V _{DS} =0V	---	---	±10	A

On Characteristics

R _{DS} (ON)	Static Drain- Source On- Resistance	V _{GS} =10V , I _D =0.3A	---	1.8	2.8	Ω
		V _{GS} =4.5V , I _D =0.2A	---	2.2	3	Ω
V _{GS} (th)	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250uA	1	1.6	2.5	V
ΔV _{GS} (th))	V _{GS} (th) Temperature Coefficient		---	-4	---	mV/°C
g _{fs}	Forward Transconductance	V _{DS} =10V , I _D =0. 1A	---	0.24	---	S

Dynamic and switching Characteristics

Qg	Total Gate Charge ^{2, 3}	VDS=30V , VGS=10V , ID=0.2A	---	1.1		nC
Qgs	Gate-Source Charge ^{2, 3}		---	0.1		
Qgd	Gate-Drain Charge ^{2, 3}		---	0.23		
Td(on)	Turn-On Delay Time ^{2, 3}	VDD=30V , VGS=10V , RG=6Ω ID=0.2A	---	3		nS
Tr	Rise Time ^{2, 3}		---	5		
Td(off)	Turn-Off Delay Time ^{2, 3}		---	14		
Tf	Fall Time ^{2, 3}		---	9		
Ciss	Input Capacitance	VDS=10V , VGS=0V , F=1MHz	---	30.6		pF
Coss	Output Capacitance		---	5.5		
Crss	Reverse Transfer Capacitance		---	4		

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
IS	Continuous Source Current	VG=VD=0V , Force Current	---	---	0.3	A
ISM	Pulsed Source Current		---	---	0.6	A
VSD	Diode Forward Voltage	VGS=0V , IS=1A , TJ=25	---	---	1.2	V

Note :

1. Repetitive Rating : Pulsed width limited by maximum junction temperature.
2. The data tested by pulsed , pulse width $\leq$ 300us , duty cycle $\leq$ 2%.
3. Essentially independent of operating temperature.




Fig. 1 Output Characteristics




Fig. 2 Continuous Drain Current vs. T_J




Fig. 3 Normalized $R_{DS(on)}$ vs. T_J




Fig. 4 Normalized V_{th} vs. T_J




Fig. 5 Gate Charge Waveform






Fig. 6 Capacitance Characteristics



Square Wave Pulse Duration (s)

Fig. 7 Normalized Transient Impedance



Id, Continuous Drain Current (A)

VDS, Drain to Source Voltage (V)

Fig. 8 Maximum Safe Operation Area






Fig.9 Switching Time Waveform

PACKAGE MECHANICAL DATA



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
c	0.100	0.150	0.004	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.400	0.085	0.094
e	0.650 TYP		0.026 TYP	
e1	1.200	1.400	0.047	0.055
L	0.525 REF		0.021 REF	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°

Suggested Pad Layout



- Note:**
- 1. Controlling dimension: In millimeters.
 - 2. General tolerance: ±0.05mm.
 - 3. The pad layout is for reference purposes only.

REEL

P/N	PKG	QTY
2N7002DWH6327-MS	SOT-363	3000

Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specification of any and all MSKSEMI Semiconductor products described or contained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringement of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.