









1		2		3		4		5		6		7		8																																																								
SAMZO		REAC/ROHS								REV		ECN NO		DESRIPTION		DESIGN		APPROVAL		DATE																																																		
										A1		NEW		Replace frame						2018.06.12																																																		
E									电路图 CIRCUIT DIAGRAM																																																													
D									PCB. 焊接图 PCB. WELDING DRAWING																																																													
C		LS 4 D 410 1 * 1 0 A B C D E F G H		A. 系列:LS-6. 2*6. 2mm B. 贴装方式:4-立式贴片 C. 引脚规格:D-2PIN D. 操作高度:410-4. 1mm E:操作力度:1-380gf F:操作寿命:1-200, 000/2-300, 000次 G:固定方式:1-无住 H:物料编码:0-常规																																																																		
B	主要技术参数、性能 The Main Thchnology Performance		<table><tr><td>额定电流、电压</td><td>50mA DC12V</td></tr><tr><td>接触电阻</td><td>≤50mΩ</td></tr><tr><td>按力</td><td>±50gf</td></tr><tr><td>行程</td><td>0. 7±0. 30mm</td></tr><tr><td>绝缘电阻</td><td>≥100MΩ</td></tr><tr><td>介电强度</td><td>≥250VAC/1min</td></tr></table>		额定电流、电压	50mA DC12V	接触电阻	≤50mΩ	按力	±50gf	行程	0. 7±0. 30mm	绝缘电阻	≥100MΩ	介电强度	≥250VAC/1min	<table><tr><td>F</td><td>按钮</td><td>硅胶</td><td>1</td><td>绿色</td></tr><tr><td>E</td><td>盖板</td><td>不锈钢</td><td>1</td><td>清洗</td></tr><tr><td>D</td><td>内按</td><td>PPA</td><td>1</td><td>黑色</td></tr><tr><td>C</td><td>弹片</td><td>不锈钢</td><td>2</td><td>镀银</td></tr><tr><td>B</td><td>本体</td><td>LCP</td><td>1</td><td>黑色</td></tr><tr><td>A</td><td>卡件</td><td>磷铜</td><td>1</td><td>镀银</td></tr><tr><td>项目</td><td>名称</td><td>材质</td><td>数量</td><td>表面处理/颜色</td></tr><tr><td>ITEM</td><td>DESCRIPTION</td><td>MATERIAL</td><td>QTY</td><td>FINSH/COLOR</td></tr></table>		F	按钮	硅胶	1	绿色	E	盖板	不锈钢	1	清洗	D	内按	PPA	1	黑色	C	弹片	不锈钢	2	镀银	B	本体	LCP	1	黑色	A	卡件	磷铜	1	镀银	项目	名称	材质	数量	表面处理/颜色	ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR												
					额定电流、电压	50mA DC12V																																																																
接触电阻	≤50mΩ																																																																					
按力	±50gf																																																																					
行程	0. 7±0. 30mm																																																																					
绝缘电阻	≥100MΩ																																																																					
介电强度	≥250VAC/1min																																																																					
F	按钮	硅胶	1	绿色																																																																		
E	盖板	不锈钢	1	清洗																																																																		
D	内按	PPA	1	黑色																																																																		
C	弹片	不锈钢	2	镀银																																																																		
B	本体	LCP	1	黑色																																																																		
A	卡件	磷铜	1	镀银																																																																		
项目	名称	材质	数量	表面处理/颜色																																																																		
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR																																																																		
A			<table><tr><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td colspan="2">GENERAL TOLERANCE</td></tr><tr><td></td><td></td><td></td><td>≥0~2<</td><td>±0. 15</td></tr><tr><td>DESIGN</td><td>WANGGUIFA</td><td>2018.06.12</td><td>≥2~5<</td><td>±0. 25</td></tr><tr><td>CHECKED</td><td>ZHENGUILAN</td><td>2018.06.12</td><td>≥0~2<</td><td>±0. 15</td></tr><tr><td>APPROVED</td><td>LILIANJIANG</td><td>2018.06.14</td><td>≥5</td><td>±0. 35</td></tr></table>															GENERAL TOLERANCE					≥0~2<	±0. 15	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0. 25	CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0. 15	APPROVED	LILIANJIANG	2018.06.14	≥5	±0. 35	FIRST VIEW 		The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM		TITLE: : 6. 2*6. 2*4. 1硅胶柄汽车开关		DWG NO: LS4D-P0633		PART NO: LS4D000901		MODEL NO:LS4D4101-* -10		NAME: TACT SWITCH																		
			GENERAL TOLERANCE																																																																			
			≥0~2<	±0. 15																																																																		
DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0. 25																																																																		
CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0. 15																																																																		
APPROVED	LILIANJIANG	2018.06.14	≥5	±0. 35																																																																		
		SAMZO COMPONENTS		Electronic switch and connector manufacturer																																																																		
1		2		3		4		5		6		7		8																																																								