






Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



P= With Post

默认 = W/O Post

SPECIFICATIONS

Rated Current:1.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Phosphor Bronze

Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Ordering Information

PM 127 - * - N - S - * - ** - R - P

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
3-50Pin


Type
A=Standard
B=High Pin
C=High Pin

Length
(mm)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

R=Reel
+Cap
(编带+盖)

Post
(带插)



GENERAL TOLERANCE

DIM TOL

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3.0°

制 图

DRAWING

审 核

CHECK

批 准

APPROVAL

比 例

SCALE

投 影

Projection



深圳市华灿天禄电子有限公司

ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称

1.27 双排 排母 贴片

TITLE

型高4.3 (编带+盖)

产品料号

PM127-2-N-S-4.3-XX-R

PART NO.

材 料

MATERIAL

版 本

REV.

单 位

UNITS

页 次

SHEET

A

mm

1/1