



Features

- Low gate charge
- Trench FS Technology,
- saturation voltage: $V_{CE(sat)}$,
type =1.75V, $I_C=30A$ and $T_C=25^{\circ}C$
- RoHS product



Applications

- General purpose inverters
- UPS



Absolute Ratings ($T_C=25^{\circ}C$)

Parameter	Symbol		Value	Unit
Collector-Emitter Voltage	V_{CES}		650	V
*Collector Current-continuous	I_C	$T_C=25^{\circ}C$	60	A
		$T_C=100^{\circ}C$	30	A
Collector Current-pulse(note 1)	I_{CM}		120	A
Diode RMS forward current	I_F	$T_C=25^{\circ}C$	60	A
		$T_C=100^{\circ}C$	30	A
Gate-Emitter Voltage	V_{GES}		± 20	V
Turn-off safe area	-		120	A
Surge non repetitive forward current $t_p=10ms$ sinusoidal	I_{FSM}		120	A
Power Dissipation	P_D	$T_C=25^{\circ}C$	160	W
Operating Temperature Range	T_J		$-55 \sim 175$	$^{\circ}C$
Storage Temperature Range	T_{STG}		$-55 \sim +150$	$^{\circ}C$
Maximum Lead Temperature for Soldering Purposes	T_L		300	$^{\circ}C$

*Collector current limited by maximum Junction temperature

*Notes:

1.Pulse width limited by maximum junction temperature

Thermal Characteristic







Parameter	Symbol	Tests conditions	Min	Typ	Max	Units
Off-Characteristics						
Collector-Emitter Voltage	BV_{CES}	$I_C=250\mu A, V_{GE}=0V$	650	-	-	V
Breakdown Voltage	$\Delta BV_{CES}/\Delta$	$I_C=0.5mA, \text{referenced}$	-	0.6	-	V/ $^{\circ}C$

Temperature Coefficient	T _J	to 25°C				
Zero Gate Voltage Collector Current	I _{CES}	V _{CE} =650V,V _{GE} =0V, T _C =25°C	-	-	20	μA
		V _{CE} =650V,V _{GE} =0V, T _C =175°C	-	-	2	mA
Gate-body leakage current	I _{GES}	V _{CE} =0V,V _{GE} =±20V	-	-	±200	nA
On-Characteristics						
Gate-Emitter Threshold Voltage	V _{GE(th)}	V _{CE} =V _{GE} , I _C =250uA	4.5	-	6.5	V
Collector-Emitter saturation Voltage	V _{CESAT}	V _{GE} =15V,I _C =30A, T _C =25°C	-	1.75	2.1	V
		T _C =125°C		1.95	-	
		T _C =175°C		2.1	-	
Dynamic Characteristics						
Input capacitance	C _{ies}	V _{CE} =25V, V _{GE} =0V, f=1.0MHZ, T _C =25°C	-	1830	-	pF
Output capacitance	C _{oes}		-	160	-	pF
Reverse transfer capacitance	C _{res}		-	50.3	-	pF
Total Gate Charge	Q _g	V _{CC} =520V,I _C =30A, R _G =7.9Ω,V _{GE} =15V, T _C =25°C	-	64.5	-	nC
Gate to emitter charge	Q _{ge}		-	18.1	-	
Gate to collector charge	Q _{gc}		-	23.7	-	
Gate resistance	R _g	f=1MHz,open collector	-	1.1	-	Ω
Short current	I _{sc}	V _{GE} =15V,V _{CE} =360V, T _{Jstart} ≤150°C,t≤10μs	-	150	-	A
Switching Characteristics						
Turn-On delay time	t _{d(on)}	V _{CC} =400V,I _C =30A,R _G =7.9Ω,V _{GE} =15V T _C =25°C	-	27.0	-	ns
Turn-On rise time	t _r		-	67.0	-	ns
Turn-off delay time	t _{d(off)}		-	67.0	-	ns
Turn-off Fall time	t _f		-	44.0	-	ns
Turn-on energy	E _{on}		-	0.83	-	mJ
Turn-off energy	E _{off}		-	0.36	-	mJ
Total switching Energy	E _{tot}		-	1.19	-	mJ
Turn-On delay time	t _{d(on)}	V _{CC} =400V,I _C =30A, R _G =7.9Ω,V _{GE} =15V T _C =175°C	-	27.0	-	ns
Turn-On rise time	t _r		-	68.0	-	ns
Turn-off delay time	t _{d(off)}		-	90.0	-	ns

Turn-off Fall time	t_f		-	59.0	-	ns
Turn-on energy	E_{on}		-	1.09	-	mJ
Turn-off energy	E_{off}		-	0.58	-	mJ
Total switching Energy	E_{tot}		-	1.67	-	mJ
Anti-Parallel Diode Characteristics and Maximum Ratings						
Diode Forward Voltage	V_F	$V_{GE}=0V, I_F=15A.$	-	1.5	2.2	V
Diode Reverse recovery time	t_{rr}	$V_{GE}=0V,$ $V_R=400V, I_F=30A$ $dl/dt=100A/us$ $T_C=25^{\circ}C$	-	155	-	ns
Reverse recovery charge	Q_{rr}		-	85.0	-	uC
Diode Reverse recovery Current	I_{rrm}		-	1.14	-	A
Diode Reverse recovery time	t_{rr}	$V_{GE}=0V, V_R=400V,$ $I_F=30A$ $dl/dt=100A/us$ $T_C=175^{\circ}C$	-	307	-	ns
Reverse recovery charge	Q_{rr}		-	685	-	uC
Diode Reverse recovery Current	I_{rrm}		-	3.98	-	A
Parameter	Symbol	Value				Unit
Thermal Resistance, Junction to Case	$R_{th(j-c)}$	0.77				$^{\circ}C/W$
Thermal Resistance, Junction to Case	$R_{th(j-c)}$	3.2				$^{\circ}C/W$


Marking	Package
MSG30T65FQC	TO-247

Electrical Characteristics(curves)




Diode Characteristics

$T_j = 25^\circ\text{C}, 175^\circ\text{C}$




Capacitance Characteristics

$V_{ce} = 25\text{V}, V_{ge} = 0\text{V}, f = 1\text{MHz}$




Switching Time vs. I_C (25°C)

$V_{ce} = 400\text{V}, V_{ge} = 15\text{V}, R_G = 7.9\text{ohm}$




Switching Time vs. I_C (175°C)

$V_{ce} = 400\text{V}, V_{ge} = 15\text{V}, R_G = 7.9\text{ohm}$




Switching Time vs. R_G (25°C)

$V_{ge} = 15\text{V}, V_{ce} = 400\text{V}, I_C = 30\text{A}$




Switching Time vs. R_G (175°C)


$V_{ge} = 15\text{V}, V_{ce} = 400\text{V}, I_C = 30\text{A}$




Switching Time vs. T_j
 $V_{ge}=15V, V_{ce}=400V, I_C=30A, R_g=7.9\Omega$




Switching Loss vs. T_j
 $V_{ge}=15V, V_{ce}=400V, I_C=30A, R_g=7.9\Omega$




Switching Loss vs. $I_C(25^\circ C)$
 $V_{ge}=15V, V_{ce}=400V, R_g=7.9\Omega$




Switching Loss vs. $I_C(175^\circ C)$
 $V_{ge}=15V, V_{ce}=400V, R_g=7.9\Omega$




Switching Loss vs. $R_g(25^\circ C)$
 $V_{ge}=15V, V_{ce}=400V, I_C=30A$




Switching Loss vs. $R_g(175^\circ C)$
 $V_{ge}=15V, V_{ce}=400V, I_C=30A$




Switching Loss vs. VCE(175°C)
Vge=15V, IC=30A, Rg=7.9ohm



Safe Operating Area
Tc=25°C, Vge=15V



Transient Thermal Impedance



Package Mechanical DATA

