




SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: $1000M\Omega$, Min
Contact Resistance: $20m\Omega$, Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to $+105^{\circ}$
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
 $(260^{\circ}$ C for 5 seconds)

lo. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	4.00	8.60	24	22.00	26.60	42	40.00	44.60	60	58.00	62.60
8	6.00	10.60	26	24.00	28.60	44	42.00	46.60	62	60.00	64.60
10	8.00	12.60	28	26.00	30.60	46	44.00	48.60	64	62.00	66.60
12	10.00	14.60	30	28.00	32.60	48	46.00	50.60	66	64.00	68.60
14	12.00	16.60	32	30.00	34.60	50	48.00	52.60	68	66.00	70.6
16	14.00	18.60	34	32.00	36.60	52	50.00	54.60	70	68.00	72.60
18	16.00	20.60	36	34.00	38.60	54	52.00	56.60			
20	18.00	22.60	38	36.00	40.60	56	54.00	58.60			
22	20.00	24.60	40	38.00	42.60	58	56.00	60.60			



深圳市韩下电子有限公司

UNLESS OTHEWIXE SPECIFIED TOLERANCE										DRAWM NAME: HX JN2.0-2x9P TP H6.4									
X : ± 0.3					X° : $\pm 5^{\circ}$					SIZE		A4		SCALE		N:1		PROUCT NO.	
X.X : ± 0.2					X.X° : $\pm 1^{\circ}$					REV		A		UNIT		mm		PROJECT	
X.XX : ± 0.1					X.XX° : $\pm 0.5^{\circ}$					DRAW:		黄彬		2022/04/21		CHECKED:		张伟 2022/04/21	
										APPROVED:		罗小春		2022/04/21		PAGE		1/1	