



1. 电路CIRCUIT: ON/OFF
2. 额定值 RATING: 16A 125/250VAC 3/4HP (CUL)
16 (4) A 250V~T125/55 (NEMKO/ENEC17/CQC)
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘阻抗 INSULATION RESISTANCE: >100MΩ
(500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTUE
6. 所有部件均使用环保材料
ALL MATERIALS USING MEET THE RoHS DIRECTIVE



ASSEMBLE DRAWING

NO.	DRAWING NO.	PARTS NAME	QTY PCS/SET	MATERIAL	REMARK
1	A40232	TERMINAL 1	1	C2680R-1/2H t=0.8	Tin Plated
2	A40233	TERMINAL 2	1	C2680R-1/2H t=0.8	Tin Plated
3	A40234	TERMINAL 3	1	C2680R-1/2H t=0.8	Tin Plated
4	A40231	TERMINAL CONNECT	1	C2680R-1/2H t=0.8	Silver Plated
5	A40237	SPRING	1	SUS304	
6	A40895	UP ELECTRIC CONTACT	1	AgSnO2/Cu	0.2MM UP
7	A40235	RESISTOR	1	1/8W 220K Ω	
8	A40235	NEON LAMP	1	$\phi 4 \times 10$	
9	A30959	BOTTOM KNOB	1	NYLON	白色
10	A40236	SPRING	1	HARD DRAW STEEL WIRE	
11	A30229	BODY	1	NYLON	灰色
12	A30230	KNOB	1	PP	无色透光
13		LUBRICANT	1	MALUTEMPU D NO.2	KYODO YUSHI
14	A40902	DOWN ELECTRIC CONTACT	1	AgSnO2/Cu	0.2MM UP

5		10		DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM		
4		9		RANGE	TOLERANCE				LMC 2024.06.24	SCALE		NO		
3		8		X	±0.30					MAT'L		***		
2		7		X.X	±0.20					MATERIAL NO.		DRAWING NO.		REV.
1		6		X.XX	±0.10					SS31-CWNNE-RK20-L02-R		WIF124090		AO
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.								