




REVERSE VOLTAGE: 20 --- 100 V
CURRENT: 5.0 A

Features

- ✧ Plastic package has Underwriters Laborator Flammability Classification 94V-0
- ✧ For surface mounted applications
- ✧ Low profile package
- ✧ Built-in strain relief
- ✧ Metal silicon junction, majority carrier conduction
- ✧ High surge capability
- ✧ High current capability, low forward voltage drop
- ✧ Low power loss, high efficiency
- ✧ For use in low voltage high frequency inverters, free wheeling and polarity protection applications
- ✧ Guardring for overvoltage protection
- ✧ High temperature soldering guaranteed: 250°C/10 seconds at terminals

SMA/DO-214AC



Mechanical Data

- ✧ Case: JEDEC SMA, molded plastic over passivated chip
- ✧ Polarity: Color band denotes cathode end
- ✧ Weight: 0.064 gram

Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS





Ratings at 25°C ambient temperature unless otherwise specified

		SS 52	SS 53	SS 54	SS 55	SS 56	SS 58	SS 59	SS 510	SS 515	SS 520	UNITS
Maximum recurrent peak reverse voltage	V _{RRM}	20	30	40	50	60	80	90	100	150	200	V
Maximum RMS voltage	V _{RWS}	14	21	28	35	42	56	63	70	105	140	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	80	90	100	150	200	V
Maximum average forw ord rectified current at T _L (SEE FIG.1) (NOTE 2)	I _(AV)	5.0										A
Peak forw ard surge current 8.3ms single half- sine-w ave superimposed on rated load(JEDEC Method)	I _{FSM}	175										A
Maximum instantaneous forw ard voltage at 5.0A(NOTE.1)	V _F	0.45	0.55		0.70		0.85					V
Maximum DC reverse current @T _A =25°C at rated DC blockjng voltage(NOTE1) @T _A =100°C	I _R	0.5										mA
		20					10					
Typical thermal resitance (NOTE2)	R _{θ JA} R _{θ JL}	55 17										°C/W
Operating junction temperature range	T _J	-55--- +150					-55--- +175					°C
Storage temperature range	T _{STG}	-55--- +150					-55--- +175					°C

NOTE: 1. Pulse test: 300 μs pulse width, 1% duty cycle

2. P.C.B. mounted with 0.55"X0.55" (14.0X14.0mm²) copper pad areas

Ratings AND Characteristic Curves

FIG.1 – FORWARD DERATING CURVE

FIG.2– PEAK FORWARD SURGE CURRENT

FIG.3 – TYPICAL FORWARD CHARACTERISTICS

FIG.4 – TYPICAL REVERSE CHARACTERISTICS


PACKAGE	SPQ/PCS	CARTON SPQ/PCS	CARTON SIZE/CM	CARTON GW/KG	CARTON NW/KG
SMA	5000/REEL	80000	36X30.6X31	12.00	11.00