






1		2		3		4		5		6		7		8																					
SAMZO		REAC/ROHS								REV		ECN NO		DESRIPTION		DESIGN		APPROVAL		DATE															
										A1		NEW		Replace frame						2018.06.15															
E																																			
D																																			
C	J 4 B *** * 1 1 A																																		
		A. 系列: J-6*6mm系列		B. 贴装方式: 4-立式贴片		C. 规格: B-4P		D. 操作高度: 043~4.3mm/060~6.0mm/115~11.5m(4.3~15.0)		E. E:操作力度:1~120gf/2~180gf/3~260gf/4~350gf		F:操作寿命: 1~100,000次		G:固定方式: 1-无柱		H:物料编码: A-硅胶模																			
		主要技术参数、性能																																	
		The Main Thchnology Performance																																	
		<table><tr><td>额定电流、电压 Rate voltage,current</td><td>50mA DC12V</td></tr><tr><td>接触电阻 Contact resistance</td><td>≤100mΩ</td></tr><tr><td>按力 Operating force</td><td>±50gf</td></tr><tr><td>行程 Travel</td><td>0.25±0.10mm</td></tr><tr><td>绝缘电阻 Insulated resistance</td><td>≥100MΩ</td></tr><tr><td>介电强度 Dielectric strength</td><td>≥250VAC/1min</td></tr></table>		额定电流、电压 Rate voltage,current	50mA DC12V	接触电阻 Contact resistance	≤100mΩ	按力 Operating force	±50gf	行程 Travel	0.25±0.10mm	绝缘电阻 Insulated resistance	≥100MΩ	介电强度 Dielectric strength	≥250VAC/1min																				
额定电流、电压 Rate voltage,current	50mA DC12V																																		
接触电阻 Contact resistance	≤100mΩ																																		
按力 Operating force	±50gf																																		
行程 Travel	0.25±0.10mm																																		
绝缘电阻 Insulated resistance	≥100MΩ																																		
介电强度 Dielectric strength	≥250VAC/1min																																		