



Pushing Performance  
Since 1945

# M12 CAT6a Bu gewinkelt



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 381 4806
Specification	M12 CAT6a Bu gewinkelt
HARTING eCatalogue	<a href="https://b2b.harting.com/21033814806">https://b2b.harting.com/21033814806</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Element	PCB adapter
Specification	Angled

## Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Shielding	Shielded
Number of contacts	8
Coding	X-coding
Details	Order housings separately
Pack contents	30 pieces in a tray

## Technical characteristics

Rated current	0.5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 6A Class E <sub>A</sub> up to 500 MHz
Overvoltage category	III



**Pushing Performance**  
Since 1945

## Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 100$
Isolation group	IIIa ( $175 \leq \text{CTI} < 400$ )

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-109
----------------	-----------------



Pushing Performance  
Since 1945

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	30
Net weight	15 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140138421
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)