

E	1		2		3		4		5		6		7		8				
	SAMZO		REAC/ROHS								REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE			
											A1	NEW	Replace frame			2018.06.12			
技术要求: Technical requirements: 1. 打铜底0.5-1UM, 镍底2-2.5UM, 哑锡3-5UM。 Copper base 0.5 - 1 UM, nickel base 2 - 2.5 UM, matte tin 3 - 5 UM. 2. 不得有脚变形, 毛刺等缺陷。 There shall be no defects such as pin deformation and burrs. 3. 插脚尖部符合可焊性要求。 The tip of the insertion pin shall meet the solderability requirements. 4. 螺纹需符合通止规要求。 The thread shall meet the requirements of the go and no-go gauge. 5. 材质: 黄铜H65. Material: Brass H65. 6. 过载电流: 35A Overload current: 35A 7. 螺孔为拉伸M3 The screw holes are made by stretching M3 8. 未标注尺寸公差值按GB/T1184-1996H级 Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996 665 SERISE: 6.0*6.5mm 65 HIGH: H6.5mm S WELDING: S:SMT 0 CUSTOM CODE: ROUTINE M3 SCREW HOLE: M3 拉伸M3 7.5 4 PCB LAYOUT																			
D	1.8 6.5 0.8 5.0 拉伸M3 2 10.2 2.2 拉伸M3 6.2 5.7 2																		
C																			
B																			
A	ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR						FIRST VIEW		The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM			TITLE:: 6*6.5*6.5mm (M3)			
	A	Subject	H62(Y2)	1	tin plating							GENERAL TOLERANCE				DWG NO: 665S-P002			
												≥0~2<				±0.15	SCALE	1:1	UNIT
																			MODEL NO: 66565S0M3
						DESIGN	WANGGUIFA	2018.06.12											NAME:
						CHECKED	ZHENGUILAN	2018.06.12											PCB soldering terminal
	F					APPROVED	LILIANJIANG	2018.06.14											
1		2		3		4		5		6		7		8					