








NOTE:

- 1.Rating: DC12V 50mA;
- 2.Contact Resistance: 100mΩ Max;
- 3.Insulation Resistance: 100MΩ Min;
- 4.Withstanding Voltage: AC250V For 1 Minute;
- 5.Life Cycle: 30,000 Cycle Min;
- 6.Operating Force: 160±50gf;
- 7.Travel: 0.25±0.1mm.



Circuit Diagram



PCB LAND PATTERN

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		A1	2023.3.13	更新图纸	WM	BY	APPD
					UP TO 5mm: ±0.1	ANGULAR						
5	SHRAPNEL	SUS	1	Ag-Plating	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS			
4	TERMINAL	BRASS	2	Ag-Plating	TITLE: SLIDE SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	COVER	SPCC	1	Ni-Plating	MODEL: TS-1101-050E			SCALE: 1:1	CHK'D			
2	BUTTON	LCP	1	BLACK/WHITE	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD				
1	HOUSING	LCP	1	BLACK/WHITE								
								PRO.AGL: 		REV :A1		