







SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
A200N01-0B1P51-H20C28	1	0.00	2.00
A200N01-0B2P51-H20C28	2	2.00	4.00
A200N01-0B3P51-H20C28	3	4.00	6.00
A200N01-0B4P51-H20C28	4	6.00	8.00
A200N01-0B5P51-H20C28	5	8.00	10.00
A200N01-0B6P51-H20C28	6	10.00	12.00
A200N01-0B7P51-H20C28	7	12.00	14.00
A200N01-0B8P51-H20C28	8	14.00	16.00
A200N01-0B9P51-H20C28	9	16.00	18.00
.....			
A200N01-0B40P51-H20C28	40	(40-1)x2.0	(40)x2.0

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. A200N01-0BXP51-H20C28	TITLE:2.0PH H2.0 1xnPin 180° PC2.8 PA3.9 PB2.0 L8.7 6T		
.XX ±0.20	X.X* ±1°		MANUFACTURE DWG		
.XXX ±0.10	X.XX*±0.5°				
UNITS	mm	DESIGN: Ethan	 SCALE N:A SHEET 1/1		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			