









P.C.B LAYOUT

LED COLOR					
1	2	3	4	5	6
Red	Yellow	Green	Blue	White	Red Green



发红光 L2+ → L1
发绿光 L1+ → L2

SCHEMATIC

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 160 $\pm$ 50gf.
- 6.Travel: 0.25 $\pm$ 0.1mm.
- 7.Life test: 10,000 cycles.

					TOLERANCE UNLESS SPECIFIED									
7	COVER	PC	1		<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°								
6	COVER	PET	1				A0	2024.6.3	首次发行				ZLK	
5	TERMINAL	Bronze Silver Plated	4	Ag-PLATED			NO	DATE	REVISIONS				BY	APPD
4	CONTACT	PHOSPHOR BRONZE	1				TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN	
3	LED	GaAsP/GaP	1		MODEL: TC-1193-RL-E-C5-01				SCALE: 1:1	COMPLIANT	CHK'D			
2	BUTTON	PA66	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD					
1	HOUSING	PA66	1											
NO.	PART NAME	MATERIAL	QTY	FINISHING									PRO.AGL:	