








SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $250 \pm 80\text{gf}$ (依客户需求而定) .
- 6.Travel: $0.15 \pm 0.1\text{mm}$.
- 7.life test: 10,0000 cycles.



H=1.6mm

					TOLERANCE UNLESS SPECIFIED						
6	STEM	BRASS	1	YELLOW	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A1	2024.6.25	△接触脚更改为磷铜		YKH
5	COVER	SUS	1	Ag-PLATED			NO	DATE	REVISIONS		BY APPD
4	Waterproof membrane	PI	1	YELLOW	TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN	
3	CONTACT	SUS	1	Ag-Plated	MODEL: TS-1187U-016E-01			SCALE: 1:1	COMPLIANT	CHK'D	
2	CASE	PA9T	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 HAOYU 东莞市弘皓电子有限公司			APPD		PRO.AGL: 	
1	TERMINAL	PHOSPHOR BRONZE △	4	Ag-Plated							
NO.	PART NAME	MATERIAL	QTY	FINISHING							