



1. Designed for long haul 10G Double Port Transformer Module
2. Supports four pairs of category 5 UTP cable,Cable interface for isolation and low common mode emissions.
- 3 . Low profile Surface Mount Packaging designed for Hi-Temp Reflow Process
4. Compliant with IEEE 802.3an standard for 10G Base-Z,Designed to support 1:1 Turns Ratio Transceivers.



DIMENSIONS & SCHEMATICS




Note:
1. Dimension: mm
2. Unless otherwise specified,all tolerances are: ±0.15mm

TECHNICAL SPECIFICATIONS

ACL :	120 μ H Min. @ 100 KHz, 100mV with 8mA DC Bias
Leakage Inductance:	0.35 μ H Max. @ 100KHz, 0.1V
Cw/w:	35pF Max. @ 100KHz, 0.1V
DCR:	1.00 Ω Max;Secondary: 1.2 Ω Max
Turns Ratio(±5%):	1CT:1(TX), 1CT:1(RX)
Polarity:	1-48,4-45,7-42,10-39,13-36,16-33,19-30,22-27 In-Phase
Insertion Loss:	-1.0 dB Max. @ 1-100MHz -2.0dB Max. @ 100-250MHz -3.0dB Max. @ 250-500MHz
Return Loss:	-15dB Min. @ 1-100MHz -13dB Min. @ 100-250 MHz -10dB Min. @ 250-500 MHz
Cross Talk:	-30dB Min.@ 1-500MHz
Common Mode Rejection :	-30dB Min.@ 1-500MHz
Isolation HI-POT:	1500Vrms 1mA 60S or 1650VAC 1mA 6S
Operating Temperature range:	-40°C ~ +85°C
Storage temperature range:	-40°C ~ +125°C

PACKING SPECIFICATION



1. units/reel:300PCS
- 2 reel/carton:5PCS
- 3.units/carton :1500PCS