




Features

Switching transistor

Extremely low saturation voltage


Complementary NPN type: FMMT619



SOT-23

Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
FMMT720	SOT-23	720	3000



Maxmim Ratings (Ta=25 unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	-40	V
V_{CEO}	Collector-Emitter Voltage	-40	V
V_{EBO}	Emitter-Base Voltage	-5	V
I_C	Collector Current	-0.5	A
I_{CM}	Peak Pulse Current	-4	A
P_C	Collector Power Dissipation	350	mW
$R_{\theta JA}$	Thermal Resistance From Junction To Ambient	500	°C/W
T_J, T_{stg}	Operation Junction And Storage Temperature Range	-55~+150	°C











Electrcal Charcteristics (Ta=25 unless otherwise noted)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=-100\mu A, I_E=0$	-40			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}^*$	$I_C=-10mA, I_B=0$	-40			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=-100\mu A, I_C=0$	-5			V
Collector cut-off current	I_{CBO}	$V_{CB}=-35V, I_E=0$			-0.1	μA
Collector cut-off current	I_{CES}	$V_{CE}=-35V, V_{BE}=0$			-0.1	μA
Emitter cut-off current	I_{EBO}	$V_{EB}=-4V, I_C=0$			-0.1	μA
DC current gain	$h_{FE(1)}^*$	$V_{CE}=-2V, I_C=-10mA$	300			
	$h_{FE(2)}^*$	$V_{CE}=-2V, I_C=-100mA$	300			
	$h_{FE(3)}^*$	$V_{CE}=-2V, I_C=-1A$	180			
	$h_{FE(4)}^*$	$V_{CE}=-2V, I_C=-1.5A$	60			
	$h_{FE(5)}^*$	$V_{CE}=-2V, I_C=-3A$	12			
Collector-emitter saturation voltage	$V_{CE(sat)(1)}^*$	$I_C=-0.1A, I_B=-10mA$			-40	mV
	$V_{CE(sat)(2)}^*$	$I_C=-1A, I_B=-50mA$			-220	mV
	$V_{CE(sat)(3)}^*$	$I_C=-1.5A, I_B=-100mA$			-330	mV
Base-emitter saturation voltage	$V_{BE(sat)}^*$	$I_C=-1.5A, I_B=-75mA$			-1	V
Base-emitter voltage	$V_{BE(on)}^*$	$V_{CE}=-2V, I_C=-1.5A$			-1	V
Transition frequency	f_T	$V_{CE}=-10V, I_C=-50mA, f=100MHz$	150			MHz
Collector output capacitance	C_{ob}	$V_{CB}=-10V, f=1MHz$			25	pF
Turn-on Time	$t_{(on)}$	$V_{CC}=-15V, I_C=-0.75A, I_{B1}=I_{B2}=-15mA$		40		ns
Turn-off Time	$t_{(off)}$			435		ns

*Measured under pulse conditions . Pulse width =300 μs . Duty cycle $\leq 2\%$.




Typical Characteristics







SOT-23 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.