

Features

- Very high speed: 1 MBit/s
- High isolation voltage between input and output (Viso =3750V rms)
- Operating Temperature: -40°C~100°C


HF

Applications

- Ground loop elimination
- LSTTL to TTL, LSTTL or 5-volt CMOS
- Line receiver, data transmission
- Data multiplexing
- Switching power supplies
- Pulse transformer replacement
- Computer-peripheral interface

Mechanical Data

- Case: SOP5
- Molding Compound: UL Flammability Classification Rating 94V-0
- Terminals: Matte tin-plated leads; solderability-per MIL-STD-202, Method 208



Truth Table:

LED	VO, OUTPUT
OFF	H
ON	L

Ordering Information

BL M5XX (M) (G) (X) - (U) (N) (Y)

- ① ② ③ ④ ⑤ ⑥ ⑦ ⑧
- ① Brand(BL)
 - ② Product series(M501, M511)
 - ③ Package type(SOP5:None)
 - ④ Halogen option(None :Halogen free)
 - ⑤ CTR Bank(None)
 - ⑥ Lead frame (None: Copper)
 - ⑦ Customer option 1 (0-9 or A-Z or none)
 - ⑧ Customer option 2 (0-9 or A-Z or none)

Part Number	Package	Shipping Quantity	Marking Code
BLM501	SOP5	3000 pcs / Tape & Reel	BLM501

Marking Information

- "BL" denotes brand
- "XX" denotes Product series: 01,11.
- "Y" denotes Year : A(2024), B(2025), C(2026)
- "WW" denotes Week's number
- "N" denotes the day of Week.



Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit
Emitter	Forward Current	I _F	50	mA
	Reverse Voltage	V _R	5	V
	Power Dissipation	P _D	45	mW
Detector	Collector Output	P _O	100	mW
	Output Current	I _O	16	mA
	Supply Voltage	V _{CC}	30	V
	Output Voltage	V _O	20	V

Thermal Characteristics

Parameter	Symbol	Value	Unit
Isolation Voltage ^{*2}	V _{ISO}	3750	V _{rms}
Operating Temperature	T _{OPR}	-40 ~ +100	°C
Storage Temperature Range	T _{STG}	-55 ~ +125	°C
Soldering Temperature ^{*3}	T _{SOL}	260	°C

Notes:

1. Pulse width ≤ 1μs, Duty ratio: 0.001
2. 40 to 60% RH, AC for 1 minute
3. For 10 seconds

Electrical Characteristics (@ T_A = 25°C unless otherwise specified)

Parameter		Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input	Forward Voltage	V _F	I _F = 16mA	-	1.45	1.7	V
	Reverse Breakdown Voltage	B _{VR}	I _R = 10μA	5	20	-	V
	Diode Temperature Coefficient	ΔV _F /ΔT _A	I _F = 10mA	-	-1.6	-	mV/°C
Output	High Level Supply Current	I _{CCH}	V _{CC} = 15V, I _F = 0mA V _O = Open	-		1	μA
			T _A = 0-70°C			2	μA
	Low Level Supply Current	I _{CCL}	V _{CC} = 15V, I _F = 16mA, V _O = Open	-	120	800	μA
Transfer Characteristics	High Level Output Current	I _{OH}	I _F = 0mA, V _O = 5.5V V _{CC} = 5.5V		0.001	0.5	μA
			I _F = 0mA, V _O = 15V V _{CC} = 15V		0.005	1	
			T _A = 0-70°C			50	
	Low Level Output Voltage	V _{OL}	V _{CC} = 4.5V, I _F = 16mA I _O = 3mA	-	0.1	0.4	V
			V _{CC} = 4.5V, I _F = 16mA I _O = 2.4mA		0.1	0.5	V
	Current transfer ratio	CTR	I _F = 16mA, V _{CC} = 4.5V V _O = 0.4V	19	24	80	%
			I _F = 16mA, V _{CC} = 4.5V V _O = 0.5V	15	25		
	Isolation Resistance	R _{IO}	V _{IO} = 500Vdc 40~60% R.H.	-	1×10 ¹²	-	Ω
	Floating Capacitance	C _{IO}	f = 1MHz	-	0.6	-	pF

Switching Characteristics (@ $T_A = 0^\circ\text{C} \sim 70^\circ\text{C}$, $V_{CC} = 5\text{V}$, $I_F = 16\text{mA}$, unless otherwise specified)

Parameter		Symbol	Test Condition	Min.	Typ.	Max.	Unit
Propagation Delay Time to Output HIGH Level		T_{PLH}	$I_F = 16\text{mA}$, $R_L = 1.9\text{k}\Omega$, $T_A = 25^\circ\text{C}$	-	150	800	ns
			$I_F = 16\text{mA}$, $R_L = 1.9\text{k}\Omega$			800	
Propagation Delay Time to Output Low Level		T_{PHL}	$I_F = 16\text{mA}$, $R_L = 1.9\text{k}\Omega$, $T_A = 25^\circ\text{C}$	-	200	800	ns
			$I_F = 16\text{mA}$, $R_L = 1.9\text{k}\Omega$			800	
Common Mode Transient Immunity(at Logic High)	M501	$ CM_H $	$T_A = 25^\circ\text{C}$, $I_F = 0\text{mA}$ $ V_{CM} = 10\text{V(Peak)}$ $C_L = 15\text{pF}$, $R_L = 1.9\text{k}\Omega$	5000	-	-	$\text{V}/\mu\text{s}$
	M511		$T_A = 25^\circ\text{C}$, $I_F = 0\text{mA}$ $ V_{CM} = 1500\text{V(Peak)}$ $C_L = 15\text{pF}$, $R_L = 1.9\text{k}\Omega$	15000	-	-	
Common Mode Transient Immunity (at Logic Low)	M501	$ CM_L $	$T_A = 25^\circ\text{C}$, $I_F = 16\text{mA}$ $ V_{CM} = 10\text{V(Peak)}$ $C_L = 15\text{pF}$, $R_L = 1.9\text{k}\Omega$	5000	-	-	$\text{V}/\mu\text{s}$
	M511		$T_A = 25^\circ\text{C}$, $I_F = 16\text{mA}$ $ V_{CM} = 1500\text{V(Peak)}$ $C_L = 15\text{pF}$, $R_L = 1.9\text{k}\Omega$	15000	-	-	

Ratings and Characteristics Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Fig.1 Normalized CTR vs Forward Current




Fig.2 Normalized CTR vs Temperature




Fig.3 Output Current vs Output Voltage




Fig.4 Logic High Output Current vs Temperature




Fig. 5 Propagation Delay vs Temperature




Fig.6 Propagation Delay vs Load Resistance




Fig.7 Test Circuit and Waveforms for t_{PLH} , t_{PHL} , t_r and t_f








Fig.8 Test Circuit Common Mode Transient Immunity




Package Outline Dimensions (unit: mm)


SOP5



SOLDERING FOOTPRINT (unit: mm)



Reflow soldering




	Symbol	Min	Max	Unit
Preheat temperature	T_s	150	200	°C
Preheat time	t_s	60	120	s
Ramp-up rate(T_L to T_P)			3	°C/s
Liquidus temperature	T_L	217		°C
Time above T_L	t_L	60	150	s
Peak temperature	T_p		260	°C
Time during which T_c is between ($T_P - 5$) and T_P	t_p		30	s
Ramp-down rate(T_P to T_L)			6	°C/s

Note:

Reflow soldering is recommended at the temperatures and times shown, no more than three times.

Wave soldering



Profile feature	
Average ramp-up rate	~200°C/s
Heating rate during preheat	1°C/s to 2°C/s typical; 4°C/s maximum
Final preheat temperature T_s	~130°C
Preheat time (25°C to T_s)	>60s
Peak temperature T_p	260°C
Time within peak temperature t_p	10s
Ramp-down rate	5°C/s maximum

Soldering with hand soldering iron

- Hand soldering iron is only used for product rework or sample testing.
- Hand soldering iron requirements: Temperature: 360 °C±5°C within 3s.

Pcaking

Package Type	Packing Form	Quantity per Tube & Reel	Quantity per Box	Quantity per Carton	Antistatic Bag Specification	Box Specification	Carton Specification	Note
SOP5	Reel($\phi 330$ mm)	3000 pcs/reel	2 reels /box	5 boxes /ctn	380*420mm	350*340*60mm	365*330*370mm	Guard band 200mm /min.


■Summary table

■SOP5 (Reel)

Qty/reel: 3000 pcs. Qty/box: 6000 pcs.

Qty/ctn : 30000 pcs.

Schematic: (unit:mm)



IMPORTANT NOTICE

Galaxy Microelectronics (GME) reserves the right to make changes without further notice to any product herein to make corrections, modifications, improvements, or other changes. GME does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others.