


PIN 0.64\*0.4

 $3.20 \pm 0.2$ 

2.54



A

φ1.02

LEA

|                        |                                                |
|------------------------|------------------------------------------------|
| Current Rating:        | 3Amps                                          |
| Insulation Resistance: | 1000M $\Omega$ Min                             |
| Contact Resistance:    | 20m $\Omega$ Max                               |
| Withstanding Voltage:  | AC 1000V                                       |
| Operation Temperature: | -40° to+105°                                   |
| Contact Material:      | Brass                                          |
| Standard:              | PA6T                                           |
| Insulator Material:    | Polyester(UL 94V-0)                            |
| Contact Plating:       | Gold Flash                                     |
| Max.Processing Temp:   | 240° C for30-60seconds<br>(260° C for5seconds) |

RECOMMEND P. C. B LAYOUT  
PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)



|      |         |       |         |
|------|---------|-------|---------|
| X    | : ±0.30 | X°    | : ±5°   |
| X.X  | : ±0.25 | X.X°  | : ±1°   |
| X.XX | : ±0.20 | X.XX° | : ±0.5° |

|      |    |       |     |            |                                                                                     |      |     |
|------|----|-------|-----|------------|-------------------------------------------------------------------------------------|------|-----|
| SIZE | A4 | SCALE | N:1 | PROUCT NO. |                                                                                     |      |     |
| REV  | A  | UNIT  | mm  | PROJECT    |  | PAGE | 1/1 |

|          |               |          |               |           |                |
|----------|---------------|----------|---------------|-----------|----------------|
| DRAWNED: | 黄彬 2020.11.18 | CHECKED: | 张伟 2020.11.18 | APPROVED: | 罗小春 2020.11.18 |
|----------|---------------|----------|---------------|-----------|----------------|

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1      | 0.00   | 2.54   | 11     | 25.40  | 27.94  | 21     | 50.80  | 53.34  | 31     | 76.20  | 78.74  |
| 2      | 2.54   | 5.08   | 12     | 27.94  | 30.48  | 22     | 53.34  | 55.88  | 32     | 78.74  | 81.28  |
| 3      | 5.08   | 7.62   | 13     | 30.48  | 33.02  | 23     | 55.88  | 58.42  | 33     | 81.28  | 83.82  |
| 4      | 7.62   | 10.16  | 14     | 33.02  | 35.56  | 24     | 58.42  | 60.96  | 34     | 83.82  | 86.36  |
| 5      | 10.16  | 12.70  | 15     | 35.56  | 38.10  | 25     | 60.96  | 63.50  | 35     | 86.36  | 88.90  |
| 6      | 12.70  | 15.24  | 16     | 38.10  | 40.64  | 26     | 63.50  | 66.04  | 36     | 88.90  | 91.44  |
| 7      | 15.24  | 17.78  | 17     | 40.64  | 43.18  | 27     | 66.04  | 68.58  | 37     | 91.44  | 93.98  |
| 8      | 17.78  | 20.32  | 18     | 43.18  | 45.72  | 28     | 68.58  | 71.12  | 38     | 93.98  | 96.52  |
| 9      | 20.32  | 22.86  | 19     | 45.72  | 48.26  | 29     | 71.12  | 73.66  | 39     | 96.52  | 99.06  |
| 10     | 22.86  | 25.40  | 20     | 48.26  | 50.80  | 30     | 73.66  | 76.20  | 40     | 99.06  | 101.60 |