

General Description

The 250N03 is N-ch MOSFETs with extreme high cell density, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.

Features

- Simple Drive Requirement
- Fast Switching
- Low On-Resistance

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	30	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current	250	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current	180	A
I_{DM}	Pulsed Drain Current ¹	1000	A
EAS	Single Pulse Avalanche Energy ²	1568	mJ
P_D	Total Power Dissipation	200	W
T_{STG}	Storage Temperature Range	-55 to 175	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 175	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient	---	62.5	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction-case	---	0.48	$^\circ\text{C/W}$


Product Summary

BVDSS	RDSON	ID
30V	2m Ω	250A

Applications

- DC-DC & DC-AC converters
- High current, High speed switching
- Motor control, Audio amplifiers
- Solenoid and relay drivers

TO-220/263 Pin Configuration



Type	Package	Marking
CMP250N03	TO-220	CMP250N03
CMB250N03	TO-263	CMB250N03

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	30	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=30A$	---	---	2	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	---	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=24V$, $V_{GS}=0V$	---	---	1	mA
		$V_{DS}=24V$, $V_{GS}=0V$, $T_C=55^{\circ}\text{C}$	---	---	2	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=30A$	---	40	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	5	---	Ω
Q_g	Total Gate Charge	$I_D=120A$	---	230	---	nC
Q_{gs}	Gate-Source Charge	$V_{DS}=20V$	---	25	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$	---	60	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=15V$	---	50	---	ns
T_r	Rise Time	$R_L=30\Omega$	---	110	---	
$T_{d(off)}$	Turn-Off Delay Time	$R_G=6\Omega$	---	90	---	
T_f	Fall Time	$V_{GS}=10V$	---	75	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	5600	---	pF
C_{oss}	Output Capacitance		---	1700	---	
C_{rss}	Reverse Transfer Capacitance		---	900	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	250	A
V_{SD}	Diode Forward Voltage ¹	$V_{GS}=0V$, $I_F=30A$, $T_J=25^{\circ}\text{C}$	---	---	1.1	V

Note :

1.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.2.The EAS data shows Max. rating .The test condition is $V_{DS}=30V$, $V_{GS}=10V$, $L=1\text{mH}$, $I_{AS}=56A$.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.

Typical Characteristics

