





NOTES:





- MATERIAL SPECIFICATION:
1-1. HOUSING:LCP+40%GF, UL94V-0, COLOR: BLACK.
1-2. CONTACT:COPPER ALLOY C1065.
- PLATING SPECIFICATION:
2-1. CONTACT: 50u" MIN.NICKEL UNDER PLATING OVER ALL.
GOLD PLATING ON CONTACT SEE TABLE1,AND SOLDER AREA IS TIN.
- HF COMPLIANT,ROHS COMPLIANT.
- DATE CODE: XXXXXX
DAY
WEEK
YEAR
- MECHANICAL PERFORMANCE:
5-1. DURABILITY: SEE TABLE
- ELECTRICAL PERFORMANCE:
6-1. CURRENT: 0.5A PER PIN.
6-2. LLCR: INITIAL 55mΩ MAX. ; FINAL ΔLLCR=20mΩ MAX..
- IR REFLOW:
THE TEMPERATURE SHALL BE 260±5°C MAINTAINING 10±1 SECONDS.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: NGFF M.2 M KEY 2.3H 0.5PH	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW25M-05NGFF-230B
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2205061831
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1

Assembly stack height schematic diagram

Stack-up Top Mount Single Sided Module
for 1.20 max top-side component heightStack-up Top Mount Single Sided Module
for 1.35 max top-side component heightStack-up Top Mount Single Sided Module
for 1.5 max top-side component heightHOW TO MATE AND EXTRACT
=====

MATE: ① → ④

EXTRACT: ⑤

NOTE: Mating force will generate from step 3 to step 4.



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30
X.XX ±0.25
X.XXX ±0.15

X' ±2" X.X' ±0.5"



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

NGFF M.2 M KEY 2.3H 0.5PH

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW25M-05NGFF-230B

MOLD NO.

APPROVED BY:

邱敏

DATE :




2014-02-23

DRAW NO:


HYC-2205061831

SHEET NO.

1 OF 1







RECOMMENDED PCB LAYOUT (TOP VIEW)
DEFAULT TOLERANCE ±0.05MM



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: NGFF M.2 M KEY 2.3H 0.5PH
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW25M-05NGFF-230B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2205061831
			SHEET NO. 1 OF 1



1500	9000
PCS/REEL	PCS/CARTON

		深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.* $\pm 2^{\circ}$ X.* $\pm 0.5^{\circ}$		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	
				MOLD NO.	
SCALE: 1:1 SIZE: A4		APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	
				SHEET NO.	1 OF 1